

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39-00-0219

Status:

Active

Overview:

Mini-Fit Jr.™

Description:

Mini-Fit® Male Crimp Terminal, Phosphor Bronze, Gold (Au), 18-24 AWG, Reel



Series

image - Reference only

Documents:

- [Drawing \(PDF\)](#)
- [Product Specification PS-5556-002 \(PDF\)](#)
- [Packaging Specification PK-5558-001 \(PDF\)](#)
- [Test Summary TS-5556-002 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™
Packaging Alternative	39-00-0220 (Loose)
Product Name	Mini-Fit®
UPC	800754396349

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	126.914/mg
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9A
Voltage - Maximum	600V

Material Info

Old Part Number	5558PBGS
-----------------	----------

Reference - Drawing Numbers

Packaging Specification	PK-5558-001
Product Specification	PS-5556-002
Sales Drawing	SD-5558-002
Test Summary	TS-5556-002

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
5558Series

Mates With
5556 Mini-Fit® Crimp Terminal

Use With
5559 Mini-Fit Jr.™ Plug Housing, 30068 Mini-Fit® TPA Plug Housing, 42475 Mini-Fit® BMI Plug Housing

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool	0011030044
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	0638190900

FineAdjust™ Applicator for Insulation OD 2.50-2.95mm - 18-24 AWG	<u>0639002600</u>
FineAdjust™ Applicator for Insulation OD 1.65-2.05mm - 18-24 AWG	<u>0639002900</u>
FineAdjust™ Applicator for Insulation OD 1.90-2.30mm - 18-24 AWG	<u>0639015600</u>
FineAdjust™ Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG	<u>0639023900</u>
FineAdjust™ Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only	<u>0639024800</u>
FineAdjust™ Applicator for Insulation OD 2.30-2.60mm - 18-24 AWG	<u>0639024900</u>
T2 Terminator™ for insulation OD 2.50-2.95mm - 18-24 AWG	<u>0639102600</u>
T2 Terminator™ for insulation OD 1.65 – 2.05mm – 18 – 24 AWG	<u>0639102900</u>
T2 Terminator™ for insulation OD 1.90-2.30mm - 18-24 AWG	<u>0639115600</u>
T2 Terminator™ for insulation OD 1.40-1.70mm - 18-24 AWG	<u>0639123900</u>
T2 Terminator™ for insulation OD 2.50-2.95mm optimized for 18 AWG only	<u>0639124800</u>
T2 Terminator™ for insulation OD 2.30-2.60mm - 18-24 AWG	<u>0639124900</u>

This document was generated on 07/30/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION