

## Product Search

 Item no... 

## Product Catalog

### Products

#### Lamps & LED-Lamps

#### LED lamps

#### StarLEDs

#### BA9s - T-3 1/4

BA9s, Multivoltage  
BA9s, flashing

## Markets

### Automotive

### Aviation

### Gaming

### Illumination

### Transport

### Custom Projects

## Product details

Article: 18600650



**StarLED, BA9s LED-Lamp, 48V  
AC/DC, red**

## Description

Designation: StarLED, BA9s LED-Lamp, 48V  
AC/DC, red

Product range: StarLED

## Optical features

Colour: red

Dominant Wavelength: 630 nm

Number of LEDs: 1

Typ. Luminous intensity: 200 mcd (at DC current)

## Electrical features

Operating Voltage: 48 V

Voltage type: AC/DC

Rectifier: Half wave

Voltage tolerance: 10 %

DC current: 8 mA

## Mechanical features

Socket: BA9s

Lamp size: T-3 1/4

Length: 25 mm

Diameter: 10 mm

## Thermal features

Operating temperature: -20...+60 °C

Storage temperature: -25...+80 °C

## Gallery

## Latest News

**2013-01-08**  
LEDS MADE EASY.  
>> [More details](#)

**2012-03-09**  
Successful  
surveillance audit  
according to ISO  
9001:2008  
>> [More details](#)

**2012-02-24**  
Latest Nichia LEDs in  
CML products  
>> [More details](#)



[Standard Image](#)

[Drawing](#)

Click on a small picture to select it. Click the large image to view full size.

