



Search Results

- Evaluate
- Advertisements
 - PDFReduce Insta ..
 - PDFTX6 10Gig UT ..
 - FAQ's
 - Press Releases
 - TG Terminati ..
 - Product Bulletins
 - PDFPANDUIT TG T ..
- Design a Solution
- Part Drawings
 - PDFMiniCom TX6 ..
 - Specification Sheets
 - PDFMiniCom TX6 ..
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor
- Install & Maintain
- Installation Instructions
 - PDFTX6 10Gig Sh ..

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'CJS6X88TGY-24'

Your search criteria matched only one product, shown below

CJS6X88TGY-24



- Exceeds draft requirements of TIA/EIA-568-B.2-AD10 and ISO 11801 Class E_A Edition 2.1, and IEEE 802.3an-2006 ratified standard channel requirements for supporting 10GBASE[®] -T
- Each jack is 100% tested to ensure NEXT and RL performance and is individually serialized for traceability
- Utilizes patent-pending enhanced *Giga-TX*[™]Technology for jack terminations which optimizes performance by maintaining cable pair geometry and eliminating conductor untwist
- No punchdown tool required; termination tool (EGJT) ensures conductors are fully terminated by utilizing a smooth forward motion without impact on critical internal components for maximum reliability
- Optional termination tool (TGJT) reduces termination time by 25%, ideal for high volume installations
- Can be re-terminated a minimum of twenty times
- Blue termination cap designates *10Gig*[™] Category 6A performance and provides a positive strain relief; helps control cable bend radius and securely retains wires

- Terminates 4 -pair, 22 – 26 AWG, 100 ohm, solid or stranded shielded twisted pair cable
- Termination cap is color coded for T568A and T568B wiring schemes
- Integrated strain relief with wire cap provides 360° conductive path for grounding
- .187" grounding tab provides conductive patch for grounding individual jacks
- Accepts 6 and 8-position modular plugs without damage
- Can be clearly identified with optional labels and icons

Part Number	CJS6X88TGY-24
RoHS Compliancy Status	Compliant
Part Description	Category 6A, RJ45, 10 Gb/s, 8position, 8-wire universal shielded black module with integral shield, bulk packaged.
No. of Module Spaces	1
Pricing Description	MiniCom Module, Cat 6A, Shielded, 8 pos 8 wire, TG Style, Bulk
Wiring Scheme	T568A/T568B
Min. Order UOM	PC
Min. Order Qty.	24
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.