

T50IDH0C2

Article Number: 117-05362

Double Head Tie, 12" Long, 50lb Tensile Strength, PA66, Black, 100/pkg



 Download drawing

 Download spec sheet

Base Data

Local Order Number	T50IDH0C2
Type	T50IDH
Color	Black (BK)
Features and Benefits	• The tie contains a dual locking design to secure two bundles at once. • Head design can also provide spacing between parallel bundles. • Bent tail allows for quick insertion into head.
Product Description	The double head cable tie was designed with a dual locking head to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Double Head Tie, 12" Long, 50lb Tensile Strength, PA66, Black, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial)	50.0 lbs
Minimum Tensile Strength (Metric)	225.0 N
Length L (Imperial)	12.0 "
Length L (Metric)	305.0 mm
Bundle Diameter 2nd Loop Max. (Imperial)	1.5 "
Fixation Method	None
Identification Plate Position	none
Number of Bundles	2
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.19 "
Width W (Metric)	4.7 mm
Bundle Diameter Min. (Imperial)	0.06 "
Bundle Diameter Min. (Metric)	1.6 mm
Bundle Diameter Max. (Imperial)	1.5 "
Bundle Diameter Max. (Metric)	38.1 mm
Bundle Diameter 1st Loop Max. (Imperial)	3.0 "
Bundle Diameter 1st Loop Max. (Metric)	76.2 mm
Bundle Diameter 2nd Loop Max. (Metric)	38.1 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	100
Carton Quantity	5000

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Certification/Specification	UL
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes