



Push mounts require no adhesive backing or additional mounting hardware. They are inserted into pre-drilled holes. The winged base applies pressure on the panel wall to provide a more secure mount in high vibration applications. Can be used where only one side of panel is accessible.

‡Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Ties.

Part Number:	TM2PWH25-C
Product Family:	Push Barb Cable Tie Mounts
Product Line:	Push/Tree Barb
RoHS Compliancy Status:	Compliant
Part Description:	Winged Push Barb Cable Tie Mount
Material:	Nylon 6.6
Color:	Natural
UL Recognized:	E136577
Height (In.):	.72
Height (mm):	18.3
Length (In.):	.71
Length (mm):	18.0
Width (In.):	.61
Width (mm):	15.5
CE Compliant:	CT-ACC2 / 10.96
Environment:	Indoors
Flammability Rating:	UL94 V-2
Max. Panel Thickness (In.):	.094
Max. Panel Thickness (mm):	2.3
Mounting Method:	Push Barb
Panel Hole Diameter (In.):	.250

