

8-outlet, 8-ft cord, 2160 joule with modem/fax protection - Protect It! Surge Suppressor

MODEL NUMBER: TLP808TEL



Highlights

- 8 outlets / 8-ft. cord
- 2160 joule rating
- Modem/fax surge protection
- \$150,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Applications

- Ideal for home computers and other important electrical equipment

Package Includes

- TLP808TEL
- 6-ft. telephone cord
- Instruction manual with warranty information

Description

Tripp Lite's TLP808TEL surge suppressor has 8 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. \$150,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Features

- 2160 joules AC surge suppression shields equipment from the strongest surges and line noise
- 8 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- Long 8 foot AC line cable with space-saving angle input plug conveniently reaches distant outlets
- built-in RJ11 jacks (1in/2 out) prevent surges from damaging your modem/fax/phone equipment
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection
- Integrated child-safety sliding outlet covers safely seal off all unused outlets
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- \$150,000 Ultimate Lifetime Insurance (USA and Canada Only)

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800W



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Circuit Breaker (amps)	15
Outlet quantity / type	8 NEMA 5-15R
Transformer accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 6 transformers total
Outlet safety covers	Includes built-in sliding outlet safety covers
Outlet orientation	Single row of 5, plus a second row of 3 for transformer accommodation

INPUT

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input plug features	Space-saving right angle input plug
Input cord length (ft.)	8
Input cord length (m)	2.4
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	144000

LEDS ALARMS & SWITCHES

Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status

SURGE / NOISE SUPPRESSION

AC suppression joule rating	2160
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	330/400/400
EMI / RFI filtering	Up to 40 dB

DATALINE SURGE SUPPRESSION

Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No

PHYSICAL



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (HWD/in)	11.41 x 8.66 x 2.04
Shipping Dimensions (HWD/cm)	28.98 x 22.00 x 5.18
Shipping weight (lbs)	2.06
Shipping weight (kg)	0.93
Unit Dimensions (HWD/in)	4.86 x 9.55 x 1.51
Unit Dimensions (HWD/cm)	12.34 x 24.26 x 3.84
Unit weight (lbs)	1.89
Unit weight (kg)	0.86
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting slots enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light Gray
AC line cord color	Light Gray
Style	Strip
Keyhole slot center to center measurement	Distance between horizontal slots = 75mm; Distance between vertical slots = 41.6mm
SPECIAL FEATURES	
Additional Information	Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP808TEL](#)