




UNIVERSAL THERMOSTATS

3455RC 15 AMP HIGH TEMPERATURE SERIES



3455RC

APPLICATIONS:

- Copy Machines
- Power Supplies
- Telecommunications
- Ovens

BENEFITS:


- Electrical Rating to 15 Amp 120 VAC Resistive
- Environmental Exposure 0° to 550°F (-18° to 288°C)
- U.L., C.S.A., European Approval Agency Listings
- Single Contact (SPST)
- Pre-set and Tamperproof
- High Density Ceramic Base

SHIPPED FROM STOCK

OPEN ON RISE

CLOSE ON RISE

TEMP °F				TEMP °C				TEMP °F				TEMP °C				PART NUMBER
OPEN	TOL +/-	CLOSE	TOL +/-	OPEN	TOL +/-	CLOSE	TOL +/-	OPEN	TOL +/-	CLOSE	TOL +/-	OPEN	TOL +/-	CLOSE	TOL +/-	
65	5	30	8	18	3	-1	5	70	8	35	5	21	5	2	3	3455RC-100-243
75	5	40	8	24	3	4	5	90	8	60	5	32	5	16	3	3455RC-100-244
85	5	55	8	29	3	13	5	110	8	80	5	43	5	27	3	3455RC-100-245
95	5	65	8	35	3	18	5	130	8	100	5	54	5	38	3	3455RC-100-246
105	5	75	8	41	3	24	5	150	8	120	5	66	5	49	3	3455RC-100-247
115	5	85	8	46	3	29	5	170	8	140	5	77	5	60	3	3455RC-100-248
125	5	95	8	52	3	35	5	190	8	160	5	88	5	71	3	3455RC-100-249
135	5	105	8	57	3	41	5	210	8	180	6	99	5	82	4	3455RC-100-250
145	5	115	8	63	3	46	5	230	8	200	6	110	5	93	4	3455RC-100-251
155	5	125	8	68	3	52	5									
165	5	135	8	73	3	57	5									
175	5	145	8	79	3	63	5									
185	5	155	8	85	3	68	5									
195	5	165	8	91	3	73	5									
205	6	175	8	96	4	79	5									
215	6	185	8	102	4	85	5									
225	6	195	8	107	4	91	5									
235	6	205	8	113	4	96	5									
245	6	215	8	118	4	102	5									
255	7	225	8	124	4	107	5									
275	7	245	8	135	4	118	5									
295	7	265	8	146	4	129	5									
315	10	275	15	157	6	135	8									



RATINGS — RESISTIVE

CATALOG ELECTRICAL TYPE	120 VAC	240 VAC	277 VAC
	15 AMP	10 AMP	10 AMP
	4.4 FLA 26.4 LRA	2.2 FLA 13.2 LRA	—
	5.8 FLA 34.8 LRA	2.9 FLA 17.4 LRA	—
	125 VA	125 VA	—

FLA: Full Load Amps

LRA: Locked Rotor Amps