




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT<br>PART NO. | FLANGE<br>THICKNESS              | WEIGHT<br>lbs 10<br>(g) pcs |
|---------------------|----------------------------------|-----------------------------|
| JP75HBC25R - ---    | 0.125 - 0.25<br>(3.18 - 6.35)    | 1.96<br>(889.04)            |
| JP75HBC50R - ---    | 0.3125 - 0.50<br>(7.94 - 12.7)   |                             |
| JP75HBC75R - ---    | 0.5625 - 0.75<br>(14.29 - 19.05) |                             |



NOTES:

- NOTES:
1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PRODUCT COLOR.
  2. HOOK MATERIAL: NYLON 6/6  
ANGLE BRACKET MATERIAL: PRE-GALVANIZED STEEL  
RIVET MATERIAL: ALUMINUM  
CLAMP MATERIAL: SPRING STEEL  
NUT MATERIAL: PLATED STEEL
  3. PRODUCT IS DESIGNED TO SUPPORT A MAXIMUM OF 3/4" (19.05) DIAMETER BUNDLE. MAXIMUM RECOMMENDED STATIC LOAD: 15 lbs.
  4. PRODUCT INCORPORATES FEATURES ALLOWING USER TO RETAIN CABLE BUNDLES IN J-PRO J-HOOK WITH TAK-TY CABLE TIES UP TO 3/4" WIDE.
  5. PRODUCT MARKINGS:  
cULus logo and statement:  
"SUITABLE FOR USE IN AIR HANDLING SPACES IN ACCORDANCE WITH SECTION 300-22 (C) & (D) OF THE NATIONAL ELECTRIC CODE."  
ULC logo and statement:  
"IN ACCORDANCE WITH CAN/ULC S-102.2 IN SINGLE UNITS OR PAIRS, 4 ft (1220mm) MIN. SPACING, FSR=0, SDC=20."

|                                                                                                                                          |                          |                                                                                               |          |
|------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|-----------------------------------------------------------------------------------------------|----------|
| DIMENSIONS IN BRACKETS ARE METRIC [ mm ]                                                                                                 |                          |                                                                                               |          |
| CAD FILENAME/LAYERS<br>10K016CG_DC_GB3043BH/01A                                                                                          |                          |                                                                                               |          |
| <div>PANDUIT</div> <div>CORP.                      TINLEY PARK, ILLINOIS</div>                                                           |                          |                                                                                               |          |
| J-PRO J-HOOK WITH 360°<br>HAMMER-ON BEAM CLAMP<br>(JP75HBC__R-__)                                                                        |                          |                                                                                               |          |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X)    ±0.05 (1.3) (.XXX) ±0.010 (0.25 )<br>(.XX) ±0.02 (0.5) ANGLES ± 5° |                          | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION. |          |
| DRAWN BY<br>JAD                                                                                                                          | MAT'L:<br><br>SEE NOTE 2 | SCALE<br>NONE                                                                                 |          |
| DATE<br>1/5/06                                                                                                                           |                          | DRAWING NO.<br>GB3043BH                                                                       | DWG<br>A |
| CHK'D<br>KLN                                                                                                                             |                          | SIZE                                                                                          |          |

|     |         |      |     |                         |          |     |      |     |
|-----|---------|------|-----|-------------------------|----------|-----|------|-----|
| OIA | 11/9/10 | ARHA | DJW | CHANGED FILENAME FORMAT | GB3043BH | OIA | KLN  |     |
| R   | 1/5/06  | JAD  |     | INITIAL RELEASE         | GB3043BH | R   |      |     |
| REV | DATE    | BY   | CHK | DESCRIPTION             | ECN      | - R | CUST | SUP |