

**Ratings:**

|                           |           |
|---------------------------|-----------|
| Current                   | 8A        |
| Voltage                   | 300 V     |
| Wire Size                 | 28-16AWG  |
| Test Voltage / Dirt Level | 4.0 kV/3  |
| Rated Torque / Screw Size | 0.4Nm /M2 |

**Rated Cross Section:**



|                             |                    |
|-----------------------------|--------------------|
| Single Wire (solid)         | 1.5mm <sup>2</sup> |
| Stranded Wire (flexible)    | 1.0mm <sup>2</sup> |
| Stranded Wire with Ferrules | 1.0mm <sup>2</sup> |

**Dimensions:**

|                 |        |
|-----------------|--------|
| Spacing         | 3.81mm |
| Stripped Length | 7.0mm  |

**Materials:**

|                     |              |
|---------------------|--------------|
| Insulating Material | PA           |
| Flammability        | UL94V-0      |
| Temperature         | -30°C/+105°C |
| Block               | CuZn         |
| Contact             | CuSn         |
| Color               | Green        |



ON - SHORE TECHNOLOGY, INC.

Part Number

EDZ1700/[\*][\*]

\* - NUMBER OF POSITIONS

Units

mm

Drawing

Reviewed

Approved

Date

2/15/99

Sheet 1 of 1

Rev. A