

Choose your language: English(US)

Search Product:

Submit

[[Advanced](#)]

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

[SECURITY PRODUCTS](#) > [COLOR CAMERAS](#) > [COLOR CAMERAS WITH HOUSING](#) > [COLOR CAMERAS WITH HOUSING, WITH AUDIO](#) >



MINI COLOR CMOS CAMERA WITH AUDIO + POWER ADAPTER

Order Code: CAMCOLMBLAHU



Specifications

- ? pick-up element: 1/3" colour CMOS
- ? number of pixels: 628 x 582
- ? scanning system: NTSC
- ? resolution: 380 TV lines
- ? min. illumination: 1.5 Lux / F2.0
- ? S/N ratio: >48dB
- ? electronic shutter: 1/50 to 1/15000 sec
- ? gamma correction: 0.45
- ? automatic adjustments:
 - ? exposure
 - ? gain
 - ? gamma correction
 - ? white balance
- ? standard board lens: f6mm
- ? viewing angle: 52°
- ? video output: 1.0Vpp composite, 75 ohms (yellow connector)
- ? audio output: RCA connector
- ? power supply: 8VDC / 80mA PS0801R (regulated, power adapter incl.)
- ? operating temperature: 14°F ~ 113°F
- ? storage temperature: -22°F ~ 140°F
- ? dimensions: 1 21/32" x 1 1/2" x 1 7/64"
- ? weight: 2.12oz
- ? cable length: 9 27/32"

Stock Info

- ? Inner carton:
- ? Outer Carton: 25
- ? EAN Barcode: 5410329356354
- ? Packaging: Double Blister