



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		F	REV PER EC 0512-0302-05	05DEC05	BC	GS



- 1

SUITABLE FOR FEMALE TYPE M CONNECTORS.
- 2

CONTACT SPRING: BERYLLIUM COPPER.
CONTACT BODY: BRASS.
RETAINING RING: BERYLLIUM COPPER.
- 3

CONTACT FINISH: 0.00127[.000050] MIN GOLD IN CONTACT AREA,
0.00254[.000100] MIN TIN/LEAD IN AREA "X", ALL OVER
0.00127[.000050] NICKEL.
- 4

CONTACT FINISH: 0.00076[.000030] MIN GOLD IN CONTACT AREA,
0.00254[.000100] MIN TIN/LEAD IN AREA "X", ALL OVER
0.00127[.000050] NICKEL.

OBSOLETE	4	148513-2
	3	148513-1
	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.CARBO		05DEC05		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK A.SHARPE		05DEC05		NAME POWER CONTACT, EUROCARD TYPE M, FEMALE 90', PRINTED CIRCUIT BOARD MOUNT —					
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± ±		APVD A.SHARPE		05DEC05							
				PRODUCT SPEC —									
				APPLICATION SPEC —									
MATERIAL 		FINISH		WEIGHT —		SIZE A2		CAGE CODE 00779		DRAWING NO C=148513		RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 8:1		SHEET 1 of 1		REV F			