



RUE SAINT-HENRI 11, P.O. BOX 834 - CH-2800 DELÉMONT / SWITZERLAND

Your selected product

Jumpers - Male Jumpers

Series 999

999-11-110-10

2.54 mm, Male Jumpers

Available with or without insulator, and with 2.54, 5.08 or 7.62 mm pin spacing. For use with standard socket connectors.

Technical specs.:

Insulator: Black glass filled polyester PBT-GF30-FR

Flammability: UL 94V-O

Contact: Brass CuZn36Pb3 (C36000)


Connecting pin Ø: 0.56 mm

Mechanical life: Min. 100 cycles

Rated current: 3 A

Contact resistance: Max. 10 mΩ

Dielectric strength: Min. 1000 V RMS



Ordering information RoHS-compliant parts

P Plating code

1 Gold 0.25 µm

Option

Jumpers without insulator with wire Ø 0.50 mm instead of 0.56 mm. Part numbers:

B = 2.54 mm 999-51-110-10

B = 5.08 mm 999-51-112-10

B = 7.62 mm 999-51-113-10

[General technical specs.](#)[View CAD](#)

Advanced information:

Order Codes		
999-11-110-10	View Image	

999-11-110-10

Jumpers for socket connectors,
B = 2.54 mm, not insulated
