

Product Selector Results



Link Street™ - Fast Ethernet Switches

	Number of Ports	Port Configuration	Power	I-Temp	Evaluation Board Part Numbers	Audio Video Bridging/ IEEE 1588	MAC Size	IEEE 802.1Q Dynamic VLANs Supported	Package Size	Package Type	100BASE-FX Support	QoS IEEE 802.1p Priority, 4 Queues per Port	SNMP, RMON Network Management Support
88E6031 3-Port Fast Ethernet Switch	3	2 PHYs + 1 MII or 1 PHY + 2 MII	0.4W		DB-88E6061-1		1K	16	14mm x 20mm	128-QFP	Yes: 1 PHY Port	Yes	
88E6035 3-Port Fast Ethernet Switch	3	2 PHYs + 1 MII or 1 PHY + 2 MII	0.4W		DB-88E6065-1		1K	64	14mm x 20mm	128-QFP	Yes: 1 PHY Port	Yes	Yes
88E6060 6-Port Fast Ethernet Switch	6	5 PHYs + 1 MII or 4 PHYs + 2 MII	0.7W	Yes	DB-88E6060-1		1K	0	14mm x 20mm	128-QFP	Yes: 2 PHY Ports		
88E6061/B 6-Port Fast Ethernet Switch	6	5 PHYs + 1 MII or 4 PHYs + 2 MII	0.7W	Yes	DB-88E6061-1		1K	16	14mm x 20mm	128-QFP	Yes: 2 PHY Ports	Yes	
88E6063 7-Port Fast Ethernet Switch	7	5 PHYs + 2 MII	0.9W	Yes	DB-88E6063-1		2K	16	14mm x 20mm	128-QFP	Yes: 2 PHY Ports	Yes	Yes

Product Selector Results



Link Street™ - Fast Ethernet Switches

	Number of Ports	Port Configuration	Power	I-Temp	Evaluation Board Part Numbers	Audio Video Bridging/ IEEE 1588	MAC Size	IEEE 802.1Q Dynamic VLANs Supported	Package Size	Package Type	100BASE-FX Support	QoS IEEE 802.1p Priority, 4 Queues per Port	SNMP, RMON, Network Management Support
88E6065/B 6-Port Fast Ethernet Switch	6	5 PHYs + 1 MII or 4 PHYs + 2 MII	0.7W	Yes	DB-88E6065-1		1K	64	14mm x 20mm	128-QFP	Yes: 2 PHY Ports	Yes	Yes
88E6083 10-Port Fast Ethernet Switch	10	8 PHYs + 2 MII	1.4W	Yes	RD-88E6083-1		2K	16	24mm x 24mm	216-QFP	Yes: 8 PHY Ports	Yes	Yes
88E6085 10-Port Fast Ethernet Switch	10	8 PHYs + 2 MII	1.2W	Yes	DB-88E6085-1		2K	64	20mm x 20mm	176-QFP		Yes	Yes