



Material
Operating
Temperature
Colors

SB / PA (Nylon)
-20 °C – 40 °C (-4 °F – 104 °F) (SB)
-40 °C – 100 °C (-40 °F – 212 °F) (PA)
grey RAL 7035
black RAL 9005



IG	H mm	 mm	Number SB grey	Number PA grey	Number PA black
M 12 x 1,5	5	17		1.262.1200.50	1.262.1201.50
M 16 x 1,5	5	22		1.262.1600.50	1.262.1601.50
M 20 x 1,5	6	27		1.262.2000.50	1.262.2001.50
M 25 x 1,5	7	36		1.262.2500.50	1.262.2501.50
M 32 x 1,5	7	41		1.262.3200.50	1.262.3201.50
M 40 x 1,5	7	50		1.262.4000.50	1.262.4001.50
M 50 x 1,5	8	60		1.262.5000.50	1.262.5001.50
M 63 x 1,5	8	75		1.262.6300.50	1.262.6301.50
PG 7	5	19	1.261.0700.10	1.262.0700.11	1.262.0701.11
PG 9	5	22	1.261.0900.10	1.262.0900.11	1.262.0901.11
PG 11	5	24	1.261.1100.10	1.262.1100.11	1.262.1101.11
PG 13,5	6	27	1.261.1300.10	1.262.1300.11	1.262.1301.11
PG 16	6	30	1.261.1600.10	1.262.1600.11	1.262.1601.11
PG 21	7	36	1.261.2100.10	1.262.2100.11	1.262.2101.11
PG 29	7	46	1.261.2900.10	1.262.2900.11	1.262.2901.11
PG 36	8	60	1.261.3600.10	1.262.3600.11	1.262.3601.11
PG 42	8	65	1.261.4200.10	1.262.4200.11	1.262.4201.11
PG 48	8	70	1.261.4800.10	1.262.4800.11	1.262.4801.11
3/8" NPT	7	24		1.262.3800.70	1.262.3801.70
1/2" NPT	6	27		1.262.1200.70	1.262.1201.70
3/4" NPT	7	32		1.262.3400.70	1.262.3401.70
1" NPT	7	40		1.262.1000.70	1.262.1001.70

