


In-Line PC1 and In-Line Sealed to IP66, PC1

IN-LINE



FX0180, FX0280, FX0380

- Protection Category PC1
- Fuse Sizes 5 x 20mm, 6.3 x 25mm and 6.3 x 32mm
- Screw Terminal (Solder to order)
- 10A, 50V (250V Inaccessible)
- UL Approved (Black versions only)
- Clear or black




List No.	DIM A
FX0180	60.3
FX0280	54.5
FX0380	48.6

IN-LINE



FX0185, FX0285, FX0385

- Sealed to IP66
- Protection Category PC1
- Fuse Sizes 5 x 20mm, 6.3 x 25mm and 6.3 x 32mm
- Screw Terminal (Solder to order)
- 10A, 50V (250V Inaccessible)
- UL Approved (Black versions only)
- Clear or black



List No	DIM A
FX0185	91.0
FX0285	85.2
FX0385	79.2

Specification

FX0180, FX0280, FX0380/Colour

FX0185, FX0285, FX0385/Colour

Fuse Size:	5 x 20mm 6.3 x 25mm 6.3 x 32mm	FX0380 FX0280 FX0180	5 x 20mm 6.3 x 25mm 6.3 x 32mm	FX0385 FX0285 FX0185
Cable Acceptance:	1mm ² conductor (max.)		1mm ² conductor (max.) 1mm to 2.64mm overall diameter Stepped grommet: Stage 1: 1.00mm to 1.40mm Stage 2: 1.50mm to 1.90mm Stage 3: 2.0mm to 2.64mm	