


THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



PI



CUSTOMER APPROVAL
ENGR. SIGN Math Lumer
DATE: 4-13-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. TEST CABLE FOR ALL OPENS & SHORTS.
 2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG.
PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

ITEM	QTY	1 PC	MFG.	DESCRIPTION
2				MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).
1				CONNECTOR, MODULAR PLUG, 6 POSITION, 50U\"/>

CABLE ASSEMBLY PARTS LIST

466-146-525-D	121-610-022	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	WHITE
466-146-524-D	121-610-012	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	BLACK
466-146-523-D	121-610-002	14.0 FT (4.3 M)	44.0 IN (1117.6 MM)	SILVER SATIN
466-106-522-D	121-610-021	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	WHITE
466-106-521-D	121-610-011	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	BLACK
466-106-520-D	121-610-001	10.0 FT (3.0 M)	32.0 IN (812.8 MM)	SILVER SATIN
466-076-525-D	121-610-020	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	WHITE
466-076-524-D	121-610-010	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	BLACK
466-076-523-D	121-610-000	7.0 FT (2.1 M)	24.0 IN (609.6 MM)	SILVER SATIN
466-056-522-D	121-610-023	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	WHITE
466-056-521-D	121-610-013	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	BLACK
466-056-520-D	121-610-003	5.0 FT (1.5 M)	18.0 IN (457.2 MM)	SILVER SATIN
IDI PART NUMBER	IDI CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	

TABULATION BLOCK

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
XXX ± 0.25 (6.35)

I/O INTERCONNECT

SANTA ANA, CALIFORNIA

REV. NO.

REV. NO.

REV. NO.

REV. NO.

DATE

DATE

DATE

DATE

BY

BY

BY

BY

TITLE

6P6C COIL CABLE

TO OPEN END, CABLE ASSEMBLY

PART NO. 466-XX6-52X-D

ENG. NO. 466-XX6-52X-D


CUSTOMER DIGI KEY

SCALE NONE


SHEET 1 OF 1

A		B	C	D	E	F	G	H
THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.								
DVG. NO.		ZONE		REV.		DESCRIPTION		DATE
XX6-SIX-D				X1		CUSTOMER APPROVAL		03/26/99
				X2		ADD RETRACTED LENGTH		03/29/99
								E.V.

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PART SHALL BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



P2



CUSTOMER APPROVAL
ENGR. SIGN *Math Yarnes*
DATE: 4-13-99

NOTES: UNLESS OTHERWISE SPECIFIED.

1. TEST CABLE FOR ALL OPENS & SHORTS.
2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

TABULATION BLOCK

THIRD ANGLE PROJECTION		I/O INTERCONNECT	
		SANTA ANA, CALIFORNIA	
UNLESS OTHERWISE NOTED, DIMENSIONS ARE IN INCHES (MILLIMETER)		6P6C/6P6C COIL CABLE.	
TOLERANCES: XXX ± 0.25 (6.35)		STANDARD STYLE, CABLE ASSEMBLY	
		PART NO. 466-XX6-SIX-D	
		REV. X2	
		CUSTOMER DIGI KEY	
		SCALE NONE	
		SHEET 1 OF 1	

CABLE ASSEMBLY PARTS LIST


ITEM	QTY	FT	IOI	SEE	DESCRIPTION
2	2	PCS	IOI	*TABULATION BLOCK*	MODULAR COIL CABLE, 26 AVG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).
1	1	PCS	IOI	325-661-SOX	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.
CABLE ASSEMBLY PARTS LIST					

A	B	C	D	E	F	G	H
DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED		
XX6-512-D	X1		CUSTOMER APPROVAL	03/24/99	E.V.		

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

WIRE DIAGRAM

P1	P2
1	WHITE
2	BLACK
3	RED
4	GREEN
5	YELLOW
6	BLUE



CUSTOMER APPROVAL

ENGR. SIGN Matt Aemmer
DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. CABLE TO BE BUNDLED AND TWIST TIED.
 2. TEST CABLE FOR ALL OPENS & SHORTS.
 3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

H1661-25-ND
H1661-14-ND
H1661-07-ND

466-256-512-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
466-146-512-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
466-076-512-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM

PART NUMBER
I/O INTERCONNECT



TITLE
SANTA ANA, CALIFORNIA

THIRD ANGLE PROJECTION




UNLESS OTHERWISE NOTED:
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
XXX ± 0.25 (6.35)

NO.	REV.
466-256-512-D	1
466-146-512-D	1
466-076-512-D	1

SCALE	SHEET	OF
NONE	1	1

ITEM	DESCRIPTION	TITLE
1	10' 16C MODULAR, STANDARD STYLE, WHITE, CABLE ASSEMBLY	
2		
3		
4		
5		
6		
7		
8		
9		
10		
11		
12		
13		
14		
15		
16		
17		
18		
19		
20		
21		
22		
23		
24		
25		
26		
27		
28		
29		
30		
31		
32		
33		
34		
35		
36		
37		
38		
39		
40		
41		
42		
43		
44		
45		
46		
47		
48		
49		
50		
51		
52		
53		
54		
55		
56		
57		
58		
59		
60		
61		
62		
63		
64		
65		
66		
67		
68		
69		
70		
71		
72		
73		
74		
75		
76		
77		
78		
79		
80		
81		
82		
83		
84		
85		
86		
87		
88		
89		
90		
91		
92		
93		
94		
95		
96		
97		
98		
99		
100		

CABLE ASSEMBLY PARTS LIST



466-256-502-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
466-146-502-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
466-076-502-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER	LENGTH "X"
I/O INTERCONNECT	

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES
XXX ± 0.25 (6.35)

ENG. SIGN Math Lerner

DATE: 4-12-99

CUSTOMER APPROVAL

ENG. SIGN Math Lerner

DATE: 4-12-99

NOTES: UNLESS OTHERWISE SPECIFIED.

1. CABLE TO BE BUNDLED AND TWIST TIED.

2. TEST CABLE FOR ALL OPENS & SHORTS.

3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG.

PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

2	"X"	IOI	120-610-020	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, WHITE PVC.
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.
ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION

CABLE ASSEMBLY PARTS LIST

IOI I/O INTERCONNECT

SANTA ANA, CALIFORNIA

REV. XI

SCALE: NONE

SHEET 1 OF 1



ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	"X"	IOI	120-610-010	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.


ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
1	2 PCS	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

A		B	C	D	E	F	G	H
DWG. NO.		ZONE	REV.	DESCRIPTION	DATE	APPROVED		
XX6-500-D		X1		CUSTOMER APPROVAL	03/24/99	E.V.		

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PARTS OR SUBASSEMBLIES ARE TO BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



WIRE DIAGRAM

P1	P2
1	WHITE
2	BLACK
3	RED
4	GREEN
5	YELLOW
6	BLUE


CUSTOMER APPROVAL

ENGR. SIGN Mathy Sene
DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. CABLE TO BE BUNDLED AND TWIST TIED.
 2. TEST CABLE FOR ALL OPENS & SHORTS.
 3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

H2663-25-ND
H2663-14-ND
H2663-07-ND

466-256-500-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
466-146-500-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
466-076-500-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER	LENGTH "X"
I/O INTERCONNECT	



THIRD ANGLE PROJECTION

I/O INTERCONNECT	
SANTA ANA, CALIFORNIA	
DATE	REV.
03/24/99	X1
TITLE	
6P6C MODULAR, REVERT STYLE, SILVER SATIN, CABLE ASSEMBLY	
PART NO.	466-XX6-500-D
PWG NO.	466-XX6-500-D
CUSTOMER	DIGI KEY
SCALE	NONE
SHEET	1 OF 1

MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, SILVER SATIN PVC.

CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.

CABLE ASSEMBLY PARTS LIST

DESCRIPTION

ITEM QTY MFG. IOI PART NO.

2 "X" IOI 120-610-000


1 2 PCS IOI 325-661-50X

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED
XX6-521-D		X1	CUSTOMER APPROVAL	03/24/99	E.V.

WIRE DIAGRAM

P1	OPEN END
1	WHITE
2	BLACK
3	RED
4	GREEN
5	YELLOW
6	BLUE



CUSTOMER APPROVAL
ENGR. SIGN *Mark Thomas*
DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
- CABLE TO BE BUNDLED AND TWIST TIED.
 - TEST CABLE FOR ALL OPENS & SHORTS.
 - PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

H3662-25-ND
H3662-14-ND
H3662-07-ND

466-256-521-D	25.0 FT ± 4.0 IN 762 M ± 101.6 MM
466-146-521-D	14.0 FT ± 3.0 IN 427 M ± 76.2 MM
466-076-521-D	7.0 FT ± 2.0 IN 213 M ± 50.8 MM
PART NUMBER	LENGTH "X"

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED
1) DIMENSIONS ARE IN INCHES (MILLIMETER)
2) TOLERANCES:
XXX ± 0.25 (6.35)


I/O INTERCONNECT
SANTA ANA, CALIFORNIA

6P6C MODULAR, TO OPEN END,
BLACK, CABLE ASSEMBLY

PART NO: 466-XX6-521-D
REV NO: 466-XX6-521-D
CUSTOMER: 0101 KEY
REV: X1

ITEM	QTY	MFG.	DESCRIPTION
2	1	101	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	1	101	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50U" AU, FLAT TYPE EXIT.
CABLE ASSEMBLY PARTS LIST			

1



PDS 6
PDS 1

PI

OPEN END

WIRE DIAGRAM

PI	OPEN END
1	WHITE
2	BLACK
3	RED
4	GREEN
5	YELLOW
6	BLUE

CUSTOMER APPROVAL
 ENGR. SIGN *Matt & Anne*
 DATE: 4-12-99

H3663-75-ND
 H3663-14-ND
 H3663-07-ND

- NOTES: UNLESS OTHERWISE SPECIFIED.
- CABLE TO BE BUNDLED AND TWIST TIED.
 - TEST CABLE FOR ALL OPENS & SHORTS.
 - PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

25.0 FT ± 4.0 IN
 7.62 M ± 101.6 MM

14.0 FT ± 3.0 IN
 4.27 M ± 76.2 MM

7.0 FT ± 2.0 IN
 2.13 M ± 50.8 MM

PART NUMBER
 I/O INTERCONNECT
 LENGTH "X"

I/O INTERCONNECT

SANTA ANA, CALIFORNIA



UNLESS OTHERWISE NOTED:
 1) DIMENSIONS ARE IN INCHES (MILLIMETER)
 2) TOLERANCES:
 XXX ± 0.25 (6-35)

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	"X"	IOI	120-610-000	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 6 CONDUCTOR, UNSHIELDED, SILVER SATIN PVC.
1	1 PC	IOI	325-661-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 6 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.
CABLE ASSEMBLY PARTS LIST				
TITLE: 6P6C MODULAR, TO OPEN END, SILVER SATIN, CABLE ASSEMBLY PART NO.: 466-XX6-520-D REV. NO.: 466-XX6-520-D CUSTOMER: DIGI KEY REV. X1 SCALE: NONE SHEET 1 OF 1				