

WM slope top wallmount enclosure



System accessories Page 531 Hygienic design Page 207

Material:

Type 304 stainless steel
Enclosure and door:
– 16" H x 12" W – 24" H x 20" W:
16 ga body / 16 ga door
– 24" H x 24" W – 30" H x 24" W:
16 ga body / 14 ga door
– 30" H x 30" W – 60" H x 36" W:
14 ga body / 14 ga door

Surface finish:

– Enclosure and door: #4 Brushed
– Mounting panel: Zinc-plated

Protection rating:

UL Type 1, 12, 3R, 4, 4X
UL/cUL
UL file #: E170282


Part number overview:

See page 838

Configuration:

– 20° overhanging sloped roof
– Slotted head spring loaded insert

- One-piece body
- Foamed-in-place gasket
- Recessed blind nuts for mounting to wall
- Enclosures less than 20" high have one ¼ turn latch, 20 - 40" high have two ¼ turn latches, 42" or higher have L-Handle and three point lock rod system
- Includes mounting panel



Depth: 8" (210 mm), Height: 16 - 24" (395 - 595 mm)

Height (H1) inches (mm)	PU	16 (395)	16 (395)	20 (495)	20 (495)	24 (595)	24 (595)	Page
Width (B1) inches (mm)		12 (300)	16 (400)	16 (400)	20 (500)	20 (500)	24 (600)	
Depth (T1) inches (mm)		8 (210)	8 (210)	8 (210)	8 (210)	8 (210)	8 (210)	
Panel Height inches (mm)		15 (375)	15 (375)	19 (475)	19 (475)	22 (570)	22 (570)	
Panel Width inches (mm)		10 (254)	14 (354)	14 (354)	18 (449)	18 (449)	22 (549)	
Part No.	1	WMS161208N4	WMS161608N4	WMS201608N4	WMS202008N4	WMS242008N4	WMS242408N4	
Weight lb (kg)		21 (10)	26 (12)	34 (15)	41 (19)	47 (21)	58 (26)	

Accessories

Wallmount bracket Type 304	4	2433.000	629
----------------------------	---	----------	-----

Note: To order WM slope top enclosures in Type 316L stainless steel replace N4 ending with N6 (extended delivery times).

Depth: 8 - 12" (210 - 300 mm), Height: 20 - 36" (495 - 895 mm)

Height (H1) inches (mm)	PU	30 (755)	30 (755)	36 (895)	20 (495)	20 (495)	24 (595)	Page
Width (B1) inches (mm)		24 (600)	30 (760)	30 (760)	16 (400)	20 (500)	24 (600)	
Depth (T1) inches (mm)		8 (210)	8 (210)	8 (210)	12 (300)	12 (300)	12 (300)	
Panel Height inches (mm)		29 (730)	29 (730)	34 (870)	19 (475)	19 (475)	22 (570)	
Panel Width inches (mm)		22 (549)	28 (704)	28 (704)	14 (354)	18 (449)	22 (549)	
Part No.	1	WMS302408N4	WMS303008N4	WMS363008N4	WMS201612N4	WMS202012N4	WMS242412N4	
Weight lb (kg)		71 (32)	88 (40)	115 (52)	38 (17)	46 (21)	64 (29)	

Accessories

Wallmount bracket Type 304	4	2433.000	629
----------------------------	---	----------	-----

Note: To order WM slope top enclosures in Type 316L stainless steel replace N4 ending with N6 (extended delivery times).

WM slope top wallmount enclosure

Depth: 12 - 16" (300 - 400 mm), Height: 30 - 60" (755 -1495 mm)

Height (H1) inches (mm)	PU	30 (755)	36 (895)	36 (895)	36 (895)	48 (1195)	60 (1495)	Page
Width (B1) inches (mm)		24 (600)	30 (760)	36 (900)	30 (760)	36 (900)	36 (900)	
Depth (T1) inches (mm)		12 (300)	12 (300)	12 (300)	16 (400)	16 (400)	16 (400)	
Panel Height inches (mm)		29 (730)	34 (870)	34 (870)	34 (870)	45 (1155)	57 (1455)	
Panel Width inches (mm)		22 (549)	28 (704)	33 (840)	28 (704)	33 (840)	33 (840)	
Part No.	1	WMS302412N4	WMS363012N4	WMS363612N4	WMS363016N4	WMS483616N4	WMS603616N4	
Weight lb (kg)		79 (36)	126 (57)	153 (69)	139 (63)	209 (95)	251 (114)	

Accessories

Wallmount bracket Type 304	4	2433.000	629
----------------------------	---	----------	-----

Note: To order WM slope top enclosures in Type 316L stainless steel replace N4 ending with N6 (extended delivery times).

