

Date	Rev.	Description

L01

1.27mm FLAT RIBBON CABLE

UL File No. : E162690

UL Style : 2651

Operating Temperature : -20℃ to +105℃

Flammability Rating : UL-VW-1

Voltage Rating : 300V

Physical

Insulation Material : Polyvinyl Chloride (PVC)

Conductor : #28AWG (7*0.127) Stranded Tinned Copper

#26AWG (7*0.16) Stranded Tinned Copper

Color : Grey With Red Edge

Electrical


Impedance : 115Ω (Unbalanced)

Capacitance : 12.2 pF/ft.

Inductance : .14μH/ft.

Propagation Delay : 1.4 ns/ft.

Insulation Resistance : 1GΩ/M min.



HOW TO ORDER:

L01 - 1 - 2 - 3 - 4 UNIT - G (RoHS)

1.NO. OF CONDUCTOR	2.INSULATION MATERIAL	3.WIRE SIZE	4.CABLE LENGTH / UNIT
06 TO 64	P: PVC	A: 28 AWG B: 26 AWG	C: CM F: FEET I: INCH M: METER

DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.		
		JAMECO NO.	GOLDSUN NO.	
		643911	171-25-10	
DRAWN: Kiki Chen		Description		Rev.
VERIFY PEOPLE: Ada Zheng , Ivy Lan		CABLE RIBBON		1
		UNIT: mm	SCALE:	CAS No: ERN No:
		SHEET 1 OF 1		