





JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
7112	5.0	.021	.034	0.43	10,000	C-2R
7114	5.0	.060	.050	0.63	100,000	C-2R
7118	5.0	.115	.150	1.89	40,000	C-2R

NOTES:

- GLASS ENVELOPE TO BE TIPLESS AND SEAMLESS.
- BASE MATERIAL: NYLON OR EQUIVALENT.
- BASE COLOR: WHITE.
- PIN MATERIAL: NICKEL PLATED.
- LAMPS TO BE 100% AGED FOR AN EQUIVALENT TO A MINIMUM OF TEN HOURS AT RATED VOLTAGES.
- FINAL INSPECTION ON ALL LAMPS TO BE PER: MIL. STD. 105E TO AN AQL OF 2.5.
- DIMENSIONS NOT PROVIDING TOLERANCES ARE REFERENCE DIMENSIONS ONLY.

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE T-3/4 MICROMINIATURE BI-PIN BASED LAMPS				
A	CHANGE PIN MATERIAL NOTE		7/28/08	DRAWN BY	APPV'D BY	DATE	SIZE	FSCM NO.	DRAWING NO.	BI-PIN T-3/4	
	RELEASED - CANCEL SM-STDBP-T 3/4, 7810, 7111, BB23, 7113, 7115, 7116, 7119		3/15/00	L. WENGSTROM	L.R.	7/28/08	A	55335			
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED			SCALE	RELEASED DATE	REVISION DATE	REV. NO.	SHEET
							NONE	3/15/00	7/28/08	A	1 OF 1