


Plugs and Jacks

Nylon Insulated Banana Jacks


For standard 0.175" banana plug. Formed brass contact, bright-tinned finish. Comes with nickel-plated nut. **Panel Thickness:** to 0.343". **Current:** 15 A. **Contact Resistance:** 0.010 ohms.



| Stock No. | Mfr.'s Type | Color | EACH | | |
|-----------|--------------|--------|------|-------|---------|
| | | | 1-24 | 25-99 | 100-999 |
| 528-0157 | 108-0901-001 | White | .48 | .39 | .32 |
| 528-0158 | 108-0902-001 | Red | .48 | .39 | .32 |
| 528-0159 | 108-0903-001 | Black | .48 | .39 | .32 |
| 528-0160 | 108-0904-001 | Green | .48 | .39 | .32 |
| 528-0161 | 108-0906-001 | Orange | .48 | .39 | .32 |
| 528-0162 | 108-0907-001 | Yellow | .48 | .39 | .32 |
| 528-0163 | 108-0908-001 | Brown | .48 | .39 | .32 |
| 528-0164 | 108-0910-001 | Blue | .48 | .39 | .32 |
| 528-0165 | 108-0912-001 | Violet | .48 | .39 | .32 |
| 528-0166 | 108-0913-001 | Gray | .48 | .39 | .32 |

Insulated Metal-Clad — Military Type Tip Jacks


For 0.080" diameter standard tip plug. Comes with nylon body and nickel-plated brass jacket. Gold-plated turret terminal contact with wrap-around beryllium copper spring. Comes with nickel-plated washer and nut. Mounts in panels 0.218" thick. **Breakdown Voltage:** 5700 Vrms. **Current:** 10 A. Conform with MS-16108, Rev. F of MIL-STD-242A and MIL-C-39024/10.



| Stock No. | Mfr.'s Type | Color | EACH | | |
|-----------|--------------|--------|------|-------|---------|
| | | | 1-24 | 25-99 | 100-999 |
| 528-0107 | 105-0201-200 | White | 2.25 | 1.83 | 1.51 |
| 528-0108 | 105-0202-200 | Red | 2.25 | 1.83 | 1.51 |
| 528-0109 | 105-0203-200 | Black | 2.25 | 1.83 | 1.51 |
| 528-0110 | 105-0204-200 | Green | 2.25 | 1.83 | 1.51 |
| 528-0111 | 105-0207-200 | Yellow | 2.25 | 1.83 | 1.51 |
| 528-0112 | 105-0210-200 | Blue | 2.25 | 1.83 | 1.51 |

Insulated Metal-Clad Standard Tip Jacks

For 0.080" diameter standard tip plug. Nylon body and nickel-plated threaded brass jacket. Silver-plated contact is phosphor bronze with slotted terminal. Comes with nickel-plated nut. Mount panels to 0.281" thick. **Breakdown Voltage:** 5700 Vrms minimum. **Current:** 10 A.



| Stock No. | Mfr.'s Type | Color | EACH | | |
|-----------|--------------|-------|------|-------|---------|
| | | | 1-24 | 25-99 | 100-999 |
| 528-0184 | 105-0251-001 | White | .95 | .77 | .64 |
| 528-0185 | 105-0252-001 | Red | .95 | .77 | .64 |
| 528-0186 | 105-0253-001 | Black | .95 | .77 | .64 |

Vertical Test Jacks

Mounts through 0.052" hole and requires minimum mounting area. Accepts 0.080" dia. tip plugs. Silver-plated machined or formed beryllium copper contacts. 5 amps.

Machined Contacts

| Stock No. | Mfr.'s Type | Color | EACH | | |
|-----------|--------------|-------|------|-------|---------|
| | | | 1-24 | 25-99 | 100-999 |
| 528-0213 | 105-0851-001 | White | .55 | .45 | .37 |
| 528-0214 | 105-0852-001 | Red | .55 | .45 | .37 |
| 528-0215 | 105-0853-001 | Black | .55 | .45 | .37 |

Formed Contacts

| | | | | | |
|----------|--------------|-------|-----|-----|-----|
| 528-0219 | 105-2201-201 | White | .49 | .40 | .33 |
| 528-0220 | 105-2202-201 | Red | .49 | .40 | .33 |
| 528-0221 | 105-2203-201 | Black | .49 | .40 | .33 |

Rib-Loc® Tip Jacks

Accept standard 0.080" diameter tip plugs. Simply press into mounting hole. Silver-plated terminals. **Current:** 5 A. **Breakdown Voltage:** 3500 Vrms. **Contact Resistance:** 0.005 ohm max.



| Stock No. | Mfr.'s Type | Color | EACH | | |
|-----------|--------------|-------|------|-------|---------|
| | | | 1-24 | 25-99 | 100-999 |
| 528-0208 | 105-1041-001 | White | 1.02 | .83 | .69 |
| 528-0209 | 105-1042-001 | Red | 1.02 | .83 | .69 |
| 528-0210 | 105-1043-001 | Black | 1.02 | .83 | .69 |

Same Day Shipments For Product In Stock

JOHNSON
Components


Insulated Solderless Banana Plugs



For standard 0.166" banana jack. Tapered insulated nylon handle. Connect with wire up to 16 gauge. Nickel-plated brass body with nickel silver plug spring. **Current:** 15 A. **Contact Resistance:** 0.010 ohms.


Insulated Metal-Clad — Military Type Tip Jacks

For 0.080" diameter standard tip plug. Comes with nylon body and nickel-plated brass jacket. Gold-plated turret terminal contact with wrap-around beryllium copper spring. Comes with nickel-plated washer and nut. Mounts in panels 0.218" thick. **Breakdown Voltage:** 5700 Vrms. **Current:** 10 A. Conform with MS-16108, Rev. F of MIL-STD-242A and MIL-C-39024/10.



| Stock No. | Mfr.'s Type | Color | EACH | | |
|-----------|--------------|--------|------|-------|---------|
| | | | 1-24 | 25-99 | 100-999 |
| 528-0147 | 108-0301-001 | White | 1.00 | .81 | .67 |
| 528-0148 | 108-0302-001 | Red | 1.00 | .81 | .67 |
| 528-0149 | 108-0303-001 | Black | 1.00 | .81 | .67 |
| 528-0304 | 108-0304-001 | Green | 1.00 | .81 | .67 |
| 528-8306 | 108-0306-001 | Orange | 1.00 | .81 | .67 |
| 528-0152 | 108-0307-001 | Yellow | 1.00 | .81 | .67 |
| 528-0310 | 108-0310-001 | Blue | 1.00 | .81 | .67 |
| 528-0155 | 108-0312-001 | Violet | 1.00 | .81 | .67 |
| 528-0156 | 108-0313-001 | Gray | 1.00 | .81 | .67 |

Insulated Banana Plugs — Hex Body, Solder Stud



For standard banana jacks of 0.166" ID. Wire can be soldered to threaded stud or flared and held by stud for solderless connection. Accept up to 16-gauge wire. Nylon insulated handle is UL approved for self extinguishing. Plug is nickel-plated brass with nickel silver spring. **Current Rating:** 15 amps. **Breakdown Voltage:** 3500 Vrms minimum. **Contact Resistance:** 0.010 ohms.

Insulated Metal-Clad Standard Tip Jacks

For 0.080" diameter standard tip plug. Nylon body, phosphor bronze contact, tin plated. **Panel Thickness:** 0.437" max. **Current:** 10 A. **Breakdown Voltage:** 5700 Vrms minimum.



| Stock No. | Mfr.'s Type | Color | EACH | | |
|-----------|-------------|-------|------|-------|---------|
| | | | 1-24 | 25-99 | 100-999 |