




N11R AM

Industrial Connectors: Circular connectors NR-series: Panel-mounted connector

Product description

Description	Panel-mounted connector with metal screw-in casing
Type	N11R AM
Order No.	932 626-106
Type of contact	male
Number of contacts	11 + PE
Conductor size	max. 0.5 mm ²
Standard	DIN 43 651
Housing Color	grey

Drawing



Technical data

Pin dimensions	1.6 mm
Rated voltage	60 V AC/DC
Rated current	5 A
Contact resistance	$\leq 5 \text{ m}\Omega$
Type of termination	crimp
Suitable cables	0.14 mm ² to 0.5 mm ²

Material

Contact surface material	Ag
Contact bearer material	PET
Housing material	PET

Environmental conditions

Protection class (IEC 60529)	IP 65
Temperature range	-40 °C to +90 °C

Packing unit

Packaging unit	10 pieces
----------------	-----------

Scope of delivery and accessories

Scope of delivery	1 panel-mounted connector, not assembled, in polythene bag with assembly instructions
Accessories to order separately	can be plugged into N11R FF, N11R EF; protective cover SHK 2, order no. 733 845-001 contacts: RSC 162/1