

- Ideal replacement for 100 W halogen or incandescent PAR38 lamps
- Dimmable
- Up to 80% energy saving
- Lifetime of 25,000 hrs



Order Code 52017

#### General Data

Lamp Socket E27  
Design Lens

#### Geometric Data

Length (mm) 131.4  
Diameter (mm) 108.5  
Weight (g) 465


#### Electric Data

Wattage 18 W  
Voltage 220-240 V  
Power Factor 0.75  
Operating Frequency 50/60 Hz

#### Photometric Data

Luminous Flux (lm) 800  
CRI 80  
CCT 2700 K – warm white  
Luminous Intensity (cd) 1650  
Beam Angle (°) 25°  
Lifetime 25,000hrs

**Equivalent to (W)** 100 W





|                            |                                      |
|----------------------------|--------------------------------------|
| <b>Order Code</b>          | 52017                                |
| <b>Product Description</b> | LED PAR38 E27 18W 2700K WW 800LM DIM |

## Technical Packaging Details

|                            |                                |
|----------------------------|--------------------------------|
| Barcode                    | 023942520177                   |
| EAN 128                    | (02)00023942520177(37)06(91)53 |
| EAN 14                     | 20023942520171                 |
| Pack Dimensions (HxWxL)    | 130 mm x 130 mm x 173 mm       |
| Pack Weight                | 615 g                          |
| Carton Qty (Shipping Unit) | 12                             |
| Carton Dimensions (HxWxL)  | 413 mm x 276 mm x 382 mm       |
| Cartons/Layer              | 6                              |
| Layers/Pallet              | 2                              |
| Units/Pallet               | 144                            |

## Photometric Diagram

52017

