








SEE TABLE



SHELL	A± 0.38	B± 0.12	C± 0.10	D± 0.25	E± 0.07
09	30.81	24.99	16.96	16.21	10.96
15	39.14	33.32	25.18	24.54	19.18
25	53.03	47.04	39.12	38.25	33.12
37	69.32	63.50	55.68	54.71	49.68

PC cord drilling dimensions(after plating)

(thickness 1.60±0.20mm)



SHELL	LEAD FREE PART NUMBER	TIN LEAD PART NUMBER	DESIGNATIONS
09	D09S24A6GV00LF	D09S24A6GV00	RECEPTACLE 9 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
15	D15S24A6GV00LF	D15S24A6GV00	RECEPTACLE 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
25	D25S24A6GV00LF	D25S24A6GV00	RECEPTACLE 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
37	D37S24A*GV00LF	D37S24A*GV00	RECEPTACLE 37 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.

V =SCREWLOCK Threaded UNC 4.40 sellers

- 4 = Performance level PL3 ≥ 200 OPERATIONS
- 6 = Performance level PL1 ≥ 500 OPERATIONS

SHELL	LEAD FREE PART NUMBER	TIN LEAD PART NUMBER	DESIGNATIONS
09	D09S24A*GI00LF	D09S24A*GI00	RECEPTACLE 9 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
15	D15S24A*GI00LF	D15S24A*GI00	RECEPTACLE 15 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
25	D25S24A*GI00LF	D25S24A*GI00	RECEPTACLE 25 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.
37	D37S24A*GI00LF	D37S24A*GI00	RECEPTACLE 37 CTS STRAIGHT-SOLDER TO BOARD-PCB HARPOON-SCREWLOCK -ELEC.CONTIN.

I =SCREWLOCK Threaded M3

- 4 = Performance level PL3 ≥ 200 OPERATIONS
- 6 = Performance level PL1 ≥ 500 OPERATIONS

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

www.fciconnect.com				surface ISO 1302		tolerance std ISO 406 ISO 1101	projection 	mm 	
				TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr	JOUBERT	2000/12/21	ANGULAR	LINEAR		0.X	±0.1	size A3	Scale 2
Eng	PESSON	2000/12/21	0.XX			0.XX	±0.1	ECN	110-0059
Chr	NIRMAL GEORGE	2010-02-23	0.XX ±2			0.XXX	±0.1		
Appr	SUDHIR VARMA	2010-02-23	Product family				D-SUB	Spec ref -	
RECEPTACLE STD EUROPE				D-SUB		Rev.			
STRAIGHT SOLDERTYPE FOR PCB 1.60mm				C01-8646-0815		E			
FCI				catalog no		CUSTOMER			
-				-		sheet 1 of 1			

rev	ecn no	dr	date
A	-	SJO	2000/12/21
B	LS05-001	MPE	2005/03/14
C	LS05-0056	LGO	2005/07/07
D	LS06-0097	LGO	2006/07/28
E	110-0059	NG	2010-02-23
-	-	-	-
-	-	-	-

European Views

