


★★★★★ 7000 Series Angulated Head Cutters

Made in the USA

Edge hardened to 63/65 Rockwell "C"

Stainless Steel Leaf Springs – Fine Cutting of Small Leads and Wires



7100 Series Angulated Head Cutters with Long Foam Cushion Grips

★★★★★ 6" Miniature Angulated Head Cutter

7175E Optimum Flush Cut Cutting Capacity .001" – .018"						
A	B	C	D	F	G	
.710"	.275"	.430"	N/A	50°	.160"	



7200 Series Angulated Head Cutters with Ergonomic Molded Grips

★★★★★ 5 1/4" Miniature Angulated Head Cutter

7275E Optimum Flush Cut Cutting Capacity .001" – .018"						
A	B	C	D	F	G	
.710"	.275"	.430"	N/A	50°	.160"	



★★★★★ 6" Medium Angulated Head Cutter

7182E Optimum Flush Cut Cutting Capacity .003" – .025"						
A	B	C	D	F	G	
.710"	.275"	.430"	N/A	50°	.220"	



★★★★★ 5 1/4" Medium Angulated Head Cutter

7282E Optimum Flush Cut Cutting Capacity .003" – .025"						
A	B	C	D	F	G	
.710"	.275"	.430"	N/A	50°	.220"	



★★★★★ 6" Large Angulated Head Cutter

7172E Maximum Flush Cut Cutting Capacity .005" – .032"						
A	B	C	D	F	G	
.710"	.275"	.430"	N/A	50°	.310"	



★★★★★ 5 1/4" Large Angulated Head Cutter

7272E Maximum Flush Cut Cutting Capacity .005" – .032"						
A	B	C	D	F	G	
.710"	.275"	.430"	N/A	50°	.310"	



★★★★★ 6" Large Angulated/Tapered Tip Cutter

7104E Maximum Flush Cut Cutting Capacity .003" – .025"						
A	B	C	D	F	G	
.500"	.275"	.430"	.025"	50°	.300"	



★★★★★ 5 1/4" Large Angulated/Tapered Tip Cutter

7204E Maximum Flush Cut Cutting Capacity .003" – .025"						
A	B	C	D	F	G	
.500"	.275"	.430"	.025"	50°	.300"	

