



### PanZone® NEMA 4X/IP66 Rated Wireless Access Point Enclosures

- NEMA 4X and IP66 rating protects against corrosion, windblown dust and rain, splashing water and hose-directed water
- Universal design accommodates the most popular Wireless Access Points including Cisco Aironet<sup>^</sup> 1200, 1230, 1240, 1250, and 1300 Series
- Fiberglass construction and aluminum mounting plate allows quick and easy access point installation
- UL508A Listed and approved
- Include pre-configured mounting template
- Provisions for padlocks to protect against tampering and theft
- Optional NEMA 4X rated fittings available in various sizes
- Optional NEMA 4X drain and vent kit
- Connectivity accessory kit (included): 2-position outlet box, Mini-Com® TX6™ PLUS Jack Module, TX6™ PLUS Patch Cord, silicone sealant and grounding cable
- Shielded connectivity accessory kit also available



**PZNWE12**



**PZNWE14**

| Part Number | Part Description | Std. Pkg. Qty. |
|-------------|------------------|----------------|
|-------------|------------------|----------------|

#### PanZone® NEMA 4X/IP66 Rated Wireless Access Point Enclosures

|                 |                                                                                                                                                                                                                                                                      |   |
|-----------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|
| <b>PZNWE12</b>  | Wireless enclosure designed for Power over Ethernet applications. Includes UTP connectivity kit. External dimensions: 13.56"H x 13.47"W x 6.56"D (344.4mm x 342.1mm x 166.6mm). Internal dimensions: 11.70"H x 11.70"W x 6.29"D (297.2mm x 297.2mm x 159.8mm).       | 1 |
| <b>PZNWE12S</b> | Wireless enclosure designed for Power over Ethernet applications. Includes shielded connectivity kit. External dimensions: 13.56"H x 13.47"W x 6.56"D (344.4mm x 342.1mm x 166.6mm). Internal dimensions: 11.70"H x 11.70"W x 6.29"D (297.2mm x 297.2mm x 159.8mm).  | 1 |
| <b>PZNWE14</b>  | Wireless enclosure designed for traditional AC power applications. Includes UTP connectivity kit. External dimensions: 15.50"H x 13.50"W x 6.25"D (393.7mm x 342.9mm x 158.8mm). Internal dimensions: 13.53"H x 11.55"W x 5.94"D (343.7mm x 293.4mm x 150.9mm).      | 1 |
| <b>PZNWE14S</b> | Wireless enclosure designed for traditional AC power applications. Includes shielded connectivity kit. External dimensions: 15.50"H x 13.50"W x 6.25"D (393.7mm x 342.9mm x 158.8mm). Internal dimensions: 13.53"H x 11.55"W x 5.94"D (343.7mm x 293.4mm x 150.9mm). | 1 |

#### NEMA 4X Rated Fittings and Accessories

|               |                                                                                                     |   |
|---------------|-----------------------------------------------------------------------------------------------------|---|
| <b>PZNF1</b>  | NEMA 4X rated compression fitting, ideal for cable diameters of .115" to .250" (2.82mm to 6.35mm).  | 1 |
| <b>PZNF2</b>  | NEMA 4X rated compression fitting, ideal for cable diameters of .230" to .395" (5.84mm to 10.03mm). | 1 |
| <b>PZNF3</b>  | NEMA 4X rated compression fitting, ideal for cable diameters of .170" to .450" (4.32mm to 11.43).   | 1 |
| <b>PZNDVK</b> | NEMA 4X drain and vent kit.                                                                         | 1 |

<sup>^</sup>Cisco and Aironet are registered trademarks of Cisco Systems, Inc.