





SPECIFICATIONS

Ratings:	50mA @ 12 VDC
Electrical Life:	300,000 cycles typical
Contact Resistance:	10mΩ max., typical @ 2-4 VDC, 100mA
Insulation Resistance:	1,000MΩ min.
Dielectric Strength:	>1,000 Vrms at sea level
Operating Force:	300 ± 50 gf




MATERIALS

Housing:	6/6 Nylon
Cover:	Polycarbonate (PC)
Lens:	Polycarbonate (PC)
Terminals:	Silver plated copper alloy
Contacts:	Silver plated phosphor bronze


HOW TO ORDER




SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.



P.C. MOUNTING



Schematic



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[720AF300GRNQ](#) [720AF300REDQ](#) [720AF300YELQ](#)