


Belegungsplan  
Loading-Plan


Schirm Shield

1	Gelb Yellow	1
2	Orange Orange	2
3	Weiß White	3
6	Blau Blue	6



4xAWG 22/7 schleppfähig/trailing	09 45 715 0061	100	m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0056	50	m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0053	20	m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0051	10	m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0027	5	m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0025	3	m
4xAWG 22/7 schleppfähig/trailing	09 45 715 0023	1,5	m
4xAWG 22/7 flexibel/stranded	09 45 715 1183	100	m
4xAWG 22/7 flexibel/stranded	09 45 715 1178	50	m
4xAWG 22/7 flexibel/stranded	09 45 715 1175	20	m
4xAWG 22/7 flexibel/stranded	09 45 715 1173	10	m
4xAWG 22/7 flexibel/stranded	09 45 715 1168	5	m
4xAWG 22/7 flexibel/stranded	09 45 715 1166	3	m
4xAWG 22/7 flexibel/stranded	09 45 715 1164	1,5	m
4xAWG 22/1 massiv/solid	09 45 715 1161	100	m
4xAWG 22/1 massiv/solid	09 45 715 1156	50	m
4xAWG 22/1 massiv/solid	09 45 715 1153	20	m
4xAWG 22/1 massiv/solid	09 45 715 1151	10	m
4xAWG 22/1 massiv/solid	09 45 715 1127	5	m
4xAWG 22/1 massiv/solid	09 45 715 1125	3	m
4xAWG 22/1 massiv/solid	09 45 715 1123	1,5	m
massiv / flexibel solid / stranded	Bestell-Nr. Part-No.	Maß a Dim. a	

Übertragungseigenschaften nach  
ISO/IEC 11801:2002: Class D  
Schutzart: IP67/65  
Temperaturbereich: -40°C ... +70°C  
Transmission properties in accordance  
with ISO/IEC 11801:2002: Class D  
Protection level: IP67/65  
Temperature range: -40°C ... +70°C



Alle Rechte vorbehalten. All rights reserved

All Dimensions in mm Original Size DIN A 3			Techn. Character.			Nicht tolerierte Maße / Free size tolerances	
Mod.	Dat.	Name	Dat.	Name	Maßstab/Scale	RJI Kabel AWG 22, IP67/65 RJI Cable AWG 22, IP67/65 2x RJ45, Metal, Data 3A	
			Detail.	28.05.03	Wae		
			Insp.	28.05.03	VSo		
32429	26.11.04	Wie	Stand.			Blatt / page	
32201	24.08.04	Wie					
32089	28.06.04	Wie	HARTING Electronics GmbH & Co. KG			Sub.	
31013			D-32339 ESPELKAMP				