




MATERIALS:

Contact: Gold Plated Beryllium Copper

Spring: Stainless Steel

Body Insulation: Glass filled nylon.

RATINGS:

Voltage: Hands free testing in controlled voltage environments: 300 Vrms Max. *For CE compliance:* not intended for hand-held use at voltage above 33 Vrms/70 Vdc.

Operating Temperature: Max 302 F (150 C)

Current: 5 Amperes

ORDERING INFORMATION:

Model 4555-color* *Example:* to order a red 4555, the order number is 4555-2

*Colors:

0 (Black), 1 (Brown), 2 (Red), 3 (Orange), 4 (Yellow), 5 (Green), 6 (Blue), 7 (Violet), 8 (Gray), 9 (White)

Sold in packages of 10 per color.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4555-02](#) [4555-6](#) [4555-7](#) [4555-3](#) [4555-4](#) [4555-8](#) [4555-5](#) [4555-1](#) [4555-9](#)