

EMI/RFI Ground Proof: Feed-Through Version (-FE)

Part Numbers		Cable Range	Thread Type & Size	Dimensions in Inches (mm)				
- 40 °F to 212 °F (- 40 °C to 100 °C)		Inches (mm)	See page 49 for thread specs	A	B	D	D	F ₁ /F
				Clearance Hole + .01" (+.25 mm)	Body Length	Thread Length Standard	Thread Length Elongated	Wrench Flats
CD07AA-FE	-	.12 - .26 (3 - 6.5)	PG 7 / 1/4" NPT	.49 (12.5)	.94 (24)	.20 (5)	-	.55 (14)
CD09AA-FE	-	.16 - .31 (4 - 8)	PG 9	.60 (15.2)	1.10 (28)	.24 (6)	-	.67 (17)
CD11AA-FE	-	.20 - .39 (5 - 10)	PG 11	.73 (18.5)	1.14 (29)	.24 (6)	-	.79 (20)
CD13AA-FE	-	.24 - .47 (6 - 12)	PG 13 / 13.5	.80 (20.3)	1.22 (31)	.26 (6.5)	-	.87 (22)
CD16AA-FE	-	.39 - .55 (10 - 14)	PG 16	.88 (22.3)	1.26 (32)	.26 (6.5)	-	.94 (24)
CD21AA-FE	-	.51 - .71 (13 - 18)	PG 21	1.12 (28.4)	1.50 (38)	.28 (7)	-	1.18 (30)
CD29AA-FE	-	.71 - .98 (18 - 25)	PG 29	1.47 (37.3)	1.69 (43)	.31 (8)	-	1.57 (40)
CD36AA-FE	-	.94 - 1.26 (24 - 32)	PG 36	1.85 (47)	1.89 (48)	.31 (8)	-	1.97 (50)
CD42AA-FE	-	1.26 - 1.50 (32 - 38)	PG 42	2.13 (54.1)	1.77 (45)	.35 (9)	-	2.24 (57)
CD48AA-FE	-	1.46 - 1.73 (37 - 44)	PG 48	2.34 (59.4)	1.81 (46)	.39 (10)	-	2.52 (64)
CD09NA-FE	-	.16 - .31 (4 - 8)	3/8" NPT	.68 (17)	1.14 (29)	.59 (15)	-	.67 (17) / .75 (19)
CD13NA-FE	-	.24 - .47 (6 - 12)	1/2" NPT	.83 (21)	1.28 (32.5)	.51 (13)	-	.87 (22) / .94 (24)
CD21NA-FE	-	.51 - .71 (13 - 18)	3/4" NPT	1.05 (27)	1.54 (39)	.51 (13)	-	1.18 (30)
CD12MA-FE	CD12DA-FE	.12 - .26 (3 - 6.5)	M12 x 1.5	.47 (12)	.98 (25)	.26 (6.5)	.39 (10)	.55 (14)
CD16MA-FE	CD16DA-FE	.20 - .39 (5 - 10)	M16 x 1.5	.63 (16)	1.26 (32)	.24 (6)	.39 (10)	.79 (20)
CD16MR-FE	CD16DR-FE	.16 - .31 (4 - 8)	M16 x 1.5	.63 (16)	1.14 (29)	.24 (6)	.39 (10)	.67 (17) / .75 (19)
CD20MA-FE	CD20DA-FE	.39 - .55 (10 - 14)	M20 x 1.5	.79 (20)	1.30 (33)	.24 (6)	.39 (10)	.94 (24)
CD20MR-FE	CD20DR-FE	.24 - .47 (6 - 12)	M20 x 1.5	.79 (20)	1.28 (32.5)	.24 (6)	.39 (10)	.87 (22)
CD25MA-FE	CD25DA-FE	.51 - .71 (13 - 18)	M25 x 1.5	.98 (25)	1.54 (39)	.28 (7)	.47 (12)	1.18 (30)
CD32MA-FE	CD32DA-FE	.71 - .98 (18 - 25)	M32 x 1.5	1.26 (32)	1.77 (45)	.31 (8)	.47 (12)	1.57 (40)
CD40MA-FE	CD40DA-FE	.94 - 1.26 (24 - 32)	M40 x 1.5	1.57 (40)	2.01 (51)	.31 (8)	.59 (15)	1.97 (50)
CD50MA-FE	CD50DA-FE	1.26 - 1.50 (32 - 38)	M50 x 1.5	1.97 (50)	2.24 (57.5)	.35 (9)	.59 (15)	2.24 (57)
CD63MA-FE	CD63DA-FE	1.46 - 1.73 (37 - 44)	M63 x 1.5	2.48 (63)	2.05 (52)	.39 (10)	.59 (15)	2.52 (64) / 2.68 (68)

Feed-Through Products are Quick, Reliable & Labor Saving!



Feed-Through (-FE)

Partial Jacket Stripping



Total Jacket Removal



Fold Shield Over Jacket




Use our recommended **EMI Locking Nuts with cutting edges** which will cut through paint to ensure proper grounding (see page 29). Also, these Locking Nuts are suitable for vibrating applications.

Dome Fittings also available with the following approvals:



www.sealconex.com



Suggested Clearance Hole for Non-Threaded Mounting



Other Optional Locking Nuts & Other Accessories starting on Page 28 - 39.



Metalized Finger for additional EMI Shielding.

For Material Specifications and Approval Information, please refer to page 45.