


THREADS: (2B)
SPECIAL: DOUBLE-LEAD .500-32
MINOR DIA.: .466/.474
PITCH DIA.: .4797/.4842
MAJOR DIA.: .500



.030 MAX
(NOTE 2)

R .020
(6X)

R .015 MAX
(6X)

NOTES:

1. NUT IS TO ACCEPT A TORQUE OF 18 LB.-IN. WITHOUT CRACKING OR STRIPPING
2. THE STARTING POINT OF THE LEAD THREAD CANNOT EXCEED .030 FROM SURFACE **A**.
3. "FLASH EXTENDING ABOVE SURFACE **A**" CANNOT EXCEED .006 HIGH AND .004 THICK.

PACKAGING NOTES:

PLACE IN TOTE -580599 LINED WITH POLY BAG -890-750
LABEL TOTE WITH -914-796 PRINTED PER GENERAL LABEL
SPEC. LS-000003.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

DENOTES CRITICAL CHARACTERISTICS.

DENOTES CPK DIMENSIONS - MINIMUM CPK VALUE

DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF THE PROCESS CAPABILITY OF THE MANUFACTURING PROCESS FOR MEASUREMENT OF THE CHARACTERISTIC. IT DOES NOT REQUIRE THE INSPECTION OF THE CHARACTERISTIC.

DENOTES CP DIMENSIONS - MINIMUM CP VALUE
DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS
APPLY FOR MAXIMUM TOOL LIFE.

1	057295	RYNITE 415 HP	DESCRIPTION	QTY/M	LB
NO	COMPONENT NO			U/M	

BILL OF MATERIAL

CPIES TO		MATERIAL SPEC		FINISH	
LTR	REVISION	DRW	KAM	DATE	SCALE
1	9	18		1/23/97	4:1
2	10	19			
3	12	20			
4	13	21			
5	14	23			
6	15	33			
7	16	43			
8	17	53			
				TOLERANCE UNLESS OTHERWISE SPECIFIED	
				TWO PLACE DEC ±.01	
				THREE PLACE DEC ±.005	
				ANGULAR ±1°	

TITLE

HEX NUT, MOLDED

Littlefuse
DES PLAINES, ILLINOIS 60016

REVISION
M

DRWG. NO.
903-097

UNCONTROLLED DOCUMENT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[903-097](#)