

PRODUCT NUMBER
95615-XXXXLF

PLATING


- 0 = 0.20µm GOLD/GXT ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
- 1 = 0.76µm GOLD/GXT ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
- 3 = 0.38µm GOLD/GXT ON CONTACT AREA
2µm MIN MATTE TIN ON TAIL
- 5 = 0.38µm GXT FULL PLATED
- 6 = 0.76µm GXT FULL PLATED
- 7 = 0.76µm GOLD/GXT FULL PLATED
- 9 = 0.20µm GOLD/GXT FULL PLATED

1.27µm Ni MIN UNDERPLATING



RoHS COMPATIBLE, SEE NOTE 6

PACKAGING, SEE NOTE 5

TOTAL NB OF POSITIONS, 08 TO 34



STANDARD PICK-UP CAP



LARGE PICK-UP CAP NOTE 5
NOT AVAILABLE FOR 2X2

NOTES:

1. MATERIAL HOUSING: HIGH TEMP. THERMOPLASTIC
UL 94V-0, COLOR CREAM
2. MATERIAL TERMINAL: COPPER ALLOY
3. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
4. 7N MIN. PIN RETENTION IN EITHER DIRECTION.
5. PACKAGING:

= POLYBAGS

T = TUBE AVAILABILITY : FROM 2x5 UP TO 2x 17

B = TUBE WITH PICK UP CAP AVAILABLE FROM 2x5 UP TO 2x 17

K = TAPE AND REEL WITHOUT PICK-UP CAP, AS AVAILABLE

A = TAPE AND REEL WITH LARGE PICK-UP CAP, AS AVAILABLE

TR = TAPE AND REEL WITH PICK-UP CAP, AS AVAILABLE.

6. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:




- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 30 SECONDES
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.

c - LABELLING:

- MEETS PACKAGING SPECS AS PER GS-14-920
- THIS PRODUCT MEETS EUROPEAN DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS DISCRIBED
IN GS-47-0004.



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO	projection 101	product family MINITEK HEADER	
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title	
T	F-23051	AMA	16.01.15	angles	.X ±0.3		SHR HEADER	
M	F07-0191	J.CO	07.09.05	linear	.XX ±0.13	scale 7:1	2.00mm SMT	
N	F08-0145	ELA	08.04.15	dr	.XXX ±0.05		dwg no	
P	F11-0071	JCO	11.06.17	engr		FCI	sheet 1 of 1 size	
R	F11-0339	JCO	11.12.06	chr			95615 A3	
S	B-19190	LMU	14.10.24	appo			type	
sheet index	revision sheet						CUSTOMER Drawing	