



Home: FFC/FPC Connectors &gt;

**Part Number: 52207-2651**

FFC/FPC Connector, Right-Angle, Surface Mount, ZIF, Top Contact Style Receptacle, 26 Circuits, Gold (Au) Contact Plating, High Barrier Packaging



Series image - Reference only

Status:  
Replacement:OBSOLETE  
52207-2660Series:  
Category:  
Overview:52207  
FFC/FPC Connectors  
FFC-FPC (SMT)

CHECK DISTRIBUTOR INVENTORY

 Add to My Parts  
 Email this pageGo to [Part Detail](#) ▾**Mates With Part(s):**[Molex Premo-Flex FFC](#). Be sure to match like plating**Product Environmental Compliance**[EU ELV](#): Product not active[EU RoHS](#): Product not active[EU RoHS Phthalates](#): Product not active[China RoHS](#):[REACH SVHC](#): Product not active[Low-Halogen Status](#): Product not active

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, &amp; Low-Halogen

Multiple Part Industry Compliance Documents

\*IPC 1752A Class C

\*IPC 1752A Class D

\*Molex Product Compliance Declaration

**Application Tooling****FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email [ProductCompliance@molex.com](mailto:ProductCompliance@molex.com)Request Molex's CMRT from [conflictminerals@molex.com](mailto:conflictminerals@molex.com)**Part Detail**

COLLAPSE ALL

## General

Status	Obsolete
Category	FFC/FPC Connectors
Series	<a href="#">52207</a>
Overview	<a href="#">FFC-FPC (SMT)</a>
Product Name	N/A
UPC	883906262150

## Physical

Circuits (Loaded)	26
Color - Resin	Natural
Contact Position	Top
Durability (mating cycles max)	30
Entry Angle	90° Angle
Flammability	94V-0
Mated Height	2.70mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	899.652/mg
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.00mm
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-30°C to +85°C
Termination Interface: Style	Surface Mount
Wire/Cable Type	FFC/FPC

## Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

## Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number.  
[Click here to visit the UL Database](#)

CSA	LR19980
UL	E29179

