




## Dimensions: mm (In)




## TERMINAL TYPES




Quick connect terminal 187 series (D)




Quick Connect Terminal




## OPERATING CHARACTERISTICS



## MOUNTING HOLES



## CONTACT CONFIGURATION



## Mechanical Specifications:

- Operating Frequency: 300 operations/min.
- Life: 5,000,000 operations min.

## Electrical Specifications:

- Rating: 10.1A/125/250VAC
- Insulation Resistance (at 500VDC): 10MΩ min.
- Dielectric Strength: 1,000VAC RMS (50-60HZ)
- Contact Resistance (Initial): 30mΩ max.
- Operating Frequency: 10-30 operations/min.
- Operating Speed: 0.1mm to 1m/sec.
- Life: 6,000~1000,000 operations min.

## Operating Characteristics:

- OF (g) max: 150
- OP (mm): 14.7 ± 0.5
- PT max: 1.90mm
- OT min (mm): 0.70
- MD max (mm): 1.20

Miniature Snap Switch  
SNS73-10-150XX-Q21

**Mountain**  
**Switch**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-73-10-150XX-Q21](#)