


SR 150



tightening torque/thread 20.0 Nm/M 10 Inspection Test Pattern Size B 14

Type	Cat.-No.		Qty.p.pck.
SR 150	41124.2	beige	5
SR 150	41124.5	blue	5

Ratings:


	UL	CSA	DIN-VDE	IEC
			611	947-7-1
Rated Voltage	600 V	600 V	1000 V	1000 V
Rated Current	275 A	275A	335 A	309 A

Max Rated Cross Section

Single Wire (solid)	35-150 mm ²
Stranded Wire (flexible)	50-150 mm ²
Wire Size	2AWG - 300 MCM

Dimensions	TS 32	TS 35
LxBxH (mm)	93x31x115	93x31x109
Stripped Length	38 mm	

SR 240



tightening torque/thread 20.0 Nm/M 10 Inspection Test Pattern Size B 16

Type	Cat.-No.		Qty.p.pck.
SR 240	41126.2	beige	5
SR 240	41126.5	blue	5

Ratings:

	UL	CSA	DIN-VDE	IEC
			611	947-7-1
Rated Voltage	600 V	600 V	1000 V	1000 V
Rated Current	370 A	370 A	453 A	415 A

Max Rated Cross Section

Single Wire (solid)	70-240 mm ²
Stranded Wire (flexible)	70-240 mm ²
Wire Size	AWG 2/0-500

Dimensions	TS 32	TS 35
LxBxH (mm)	93x36x129	93x36x123
Stripped Length	38 mm	

Type:	Cat.-No.	Qty.p.pck.	Terminal accessories	Type:	Cat.-No.	Qty.p.pck.
			End plate			
			Isolation partition			
			Separator			
HES 32 ST	2760.0	50	End bracket	HES 32 ST	2760.0	50
HES 35 ST	2761.0	50	End bracket	HES 35 ST	2761.0	50
			Test socket			
			Test plug			
			Switchable link			
			Connection sleeve			
			Screw			
AD 1/50	2806.0	50	Warning tag	AD 1/240	2808.0	50
for 1 terminal block			Warning tag	for 1 terminal block		
			Plastic screw for warning tag			
AQI 2/150	2767.2* 300A	5	External jumper	AQI 2/240	2769.2* 382A	5
AQI 3/150	2768.2* 300A	5	External jumper	AQI 3/240	2770.2* 382A	5
ISKS 8	2773.0	-	Allen key	ISKS 8	2773.0	-

* When using AQI the rated cross-section is reduced.