



Arrowtags and Marker Plates

Features and Benefits

The arrows, plates and tags are suitable for rapid marking. They can be used regardless of the circumference of the bundle, since they can be fixed using cable ties of any length (width up to 7.4 mm).

The marking plates and arrows can be fitted with Ovalgrip cable markers.

The tags can either be written manually using T82 marker pens or fitted with the appropriate labels. They can also be direct-printed using the hot stamping process. Just ask us.

AT1 will fit 7 size 50 Ovalgrip markers.

AT2 will fit 8 size 85 Ovalgrip markers.

AT3 will fit 14 size 85 Ovalgrip markers.

Application


Used with Ovalgrip markers for identifying larger pipes and cables.




A clearly better way of identifying cables and pipes.




Marker pens T82S-BK and T82R-RD.



AT1



AT2



AT3



Specifications see
page 449 in appendix.

Material Data	
Material	Polyamide 6.6 (PA66)
Colour	Natural (NA), Black (BK)
Operating Temperature	-40 °C to +85 °C Continuous, (+105 °C for 500 h)
Flammability	UL94 V2



Technical Table

Article-No.	Type	Colour	Length (L)	Width (W)	Strap Width max. (G)	Recommended Ovalgrip Size	Marker tiles per carrier	Pack Cont.
151-41119	AT1	Natural (NA)	62.5	4.70	7.40	50	7	100
151-41110	AT1	Black (BK)	62.5	4.70	7.40	50	7	100
151-41219	AT2	Natural (NA)	63.0	9.00	6.40	85	8	100
151-41210	AT2	Black (BK)	63.0	9.00	6.40	85	8	100
151-41319	AT3	Natural (NA)	100.0	9.00	6.40	85	14	100
151-41310	AT3	Black (BK)	100.0	9.00	6.40	85	14	100
Marker pens T82								
500-50820	T82S-BK	Black (BK)	—	—	—	—	—	2
500-50822	T82R-RD	Red (RD)	—	—	—	—	—	2

All dimensions in mm. Subject to technical changes.