

PRODUCT NUMBER
54775-XXX-XXLF

PLATING

1 = 0.76μm GOLD/GXT ON CONTACT AREAS

1.27μm NICKEL MIN

6 = 0.76 μ m GXT (PdNi WITH GOLD FLASH) ON CONTACT AREAS OVER 1.27 μ m NICKEL MIN (ALTERNATIVE 0.76 μ m GOLD/GXT ON CONTACT AREAS)


_____ ROHS COMPATIBLE, SEE NOTE 5

PIN STYLE	DIM "A"	"OAL"	DIM "G" MIN
01	31.0	35.0	7.00
02	31.0	35.0	10.00

NOTES:

1. HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK
2. PIN MATERIAL : PHOSPHOR BRONZE
3. 9N MIN RETENTION IN EITHER DIRECTION
4. TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS PER ROW, N x 2.54 = 20.32mm
5. ROHS COMPATIBLE PRODUCT SPECIFICATIONS

- c - LABELING:
- MEETS PACKAGING SPECS AS PER GS-14-920
- d - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code				surface			tolerance			projection		product family									
				ISO 1302			ISO 406 ISO 1001					BERGSTIK									
ltr	ecn no	dr	date	tolerances unless otherwise specified			 mm scale 5:1					title									
H	F07-0207	LMU	07.06.06	angles																	
J	F08-0148	RTR	08.03.31	linear																	
K	B-19264	LMU	14.10.31																		
E	F06-0196	LMU	06.06.13	dr	LMU	02.03.04															
F	F06-0224	JCO	06.10.09	chnr	JCO	02.04.02															
G	F07-0136	JCO	07.02.19	uppld	JCO	02.04.02															
sheet revision										dwg no											
index sheet																					
UNSHR.HEADER STRAIGHT										sheet 1 of 1			size								
										54775										A3	
										Type CUSTOMER										Drawing	