

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200730172

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (1/2"-20 UNF) Double-Ended Cordset, 3 Poles, Male (90°) to Female (Straight), 18 AWG, PVC Cable, 0.91m (3.0') Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

UL

E152210

General

Product Family

Industrial Cordsets

Series

120073

Connector End A

Micro-Change (1/2" - 20 UNF)

Connector End B

Micro-Change (1/2" - 20 UNF)

IP Rating

IP67

Material - Contact

Copper Alloy

Overview

Brad Micro-Change (M12) Connectors

Product Name

Micro-Change (1/2" - 20 UNF)

Protocol

PROFIBUS

Region

America

Type

Double Ended

UPC

78678849619

Physical

Cable Diameter

7.11mm (.280")

Cable Length

0.91m (3.0')

Color - Cable Jacket

Yellow

Coupling Style

Threaded

Gender

Female-Male

Keyway

Dual

LED Indicator

No

Material - Cable Jacket

PVC

Material - Connector Body

PVC

Material - Coupling Nut

Black Epoxy Coated Zinc

Material - O-Ring

Nitrile Rubber

Material - Plating Mating

Gold

Orientation

90° to Straight

Poles

3

Temperature Range - Operating

-20°C to +105°C

Wire Size AWG

18

Wire/Cable Type

UL 2464

Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

250V AC/DC

Material Info

Engineering Number

773032A03F030

Reference - Drawing Numbers

Sales Drawing

SD-120073-007



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
120073 Series

This document was generated on 01/20/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION