


GM TYPE



ITEM NO.	A	B	C	D	E
GM-0603	8.5±0.25	6±0.25	3±0.25	4.7±0.25	1.7±0.25
GM-0705	10.2±0.35	7.2±0.25	5±0.25	4.4±0.25	1.7±0.25
GM-1006	13.3±0.35	10±0.35	6.4±0.25	6.3±0.25	1.7±0.25
GM-1410	19.5±0.35	13.9±0.35	10.5±0.35	6.4±0.25	3.4±0.25
GM-2015	23.7±0.45	20.1±0.45	15.5±0.35	6.1±0.25	1.7±0.25
GM-2518	29.9±0.45	25.1±0.45	18.9±0.35	7.2±0.25	1.5±0.25
GM-3225	38.1±0.45	31.7±0.45	25±0.45	7.8±0.25	1.5±0.25

		MATERIAL		ITEM NO.	
		P.V.C.		GM TYPE	
SCALE		FINISH		NAME	
				GROMMET(OPEN)	
△ (. .)		TOLERANCE AS FIGURE		△ (. .)	
				01-10-2009	
				DATE	
				REVISIONS	
				K001	
				R.NO.	

