





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L2	REVISED PER ECO-09-017580	30JUL09	HMR	JO
			L3	REVISED PER ECO-10-000445	20JAN10	KK	HMR



- | | | |
|---|--|---|
| 1 | MATERIAL: HSG FLAME RETARDANT THERMOPLASTIC,
COLOR: BLACK. POSTS: PHOS BRONZE | |
| 2 | .000030 GOLD ON CONTACT AREA,
.000100—.000200 BRIGHT TIN-LEAD ON SOLDER
LEADS, ALL OVER .000050 NICKEL | |
| 3 | RECESSED DATE CODE AND CSA LOGO | |
| 4 | .000030 GOLD ON CONTACT AREA,
.000100—.000200 MATTE TIN ON SOLDER LEADS,
ALL OVER .000050 NICKEL | |
| 5 | ROHS 2002/95/EC COMPLIANT | 7 |
| 6 | PRELIMINARY PART | 7 |
| 7 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI | 7 |



SECTION M-M



ADS,	4		1.000	.600	6	14	6	7-102802-6	
		OBSOLETE	.800	.400	4	10	5	7-102802-5	
		OBSOLETE	8.300	7.900	79	160	5	7-102802-4	
		OBSOLETE	2.500	2.100	21	44	5	7-102802-3	
		OBSOLETE	7.700	7.300	73	148	5	7-102802-2	
		7 OBSOLETE	6.800	6.400	64	130	5	6-102802-9	
		OBSOLETE	4.600	4.200	42	86	5	6-102802-8	
		7 OBSOLETE	3.900	3.500	35	72	5	6-102802-7	
		NG	OBSOLETE	1.800	1.400	14	30	5	6-102802-6
			OBSOLETE	1.300	.900	9	20	5	6-102802-5
OBSOLETE	1.100		.700	7	16	5	6-102802-4		
7 OBSOLETE	1.500		1.100	11	24	5	6-102802-3		
OBSOLETE	.900		.500	5	12	5	6-102802-2		
OBSOLETE	—		—	—	—	—	—		
7 OBSOLETE	4.800		4.400	44	90	5	6-102802-0		
2	OBSOLETE		3.300	2.900	29	60	5	5-102802-9	
	OBSOLETE		2.300	1.900	19	40	5	5-102802-8	
	OBSOLETE		3.800	3.400	34	70	5	5-102802-7	
	7 OBSOLETE	5.300	4.900	49	100	5	5-102802-6		
	OBSOLETE	4.300	3.900	39	80	5	5-102802-5		
	OBSOLETE	2.800	2.400	24	50	5	5-102802-4		
	7 OBSOLETE	2.100	1.700	17	36	5	5-102802-3		
	OBSOLETE	6.300	5.900	59	120	5	5-102802-2		
	7	OBSOLETE	—	—	—	—	—	—	
		7 OBSOLETE	.800	.400	4	10	2-102802-5		
OBSOLETE		8.300	7.900	79	160	2-102802-4			
OBSOLETE		2.500	2.100	21	44	2-102802-3			
OBSOLETE		7.700	7.300	73	148	2-102802-2			
7 OBSOLETE		6.800	6.400	64	130	1-102802-9			
OBSOLETE		4.600	4.200	42	86	1-102802-8			
OBSOLETE		3.900	3.500	35	72	1-102802-7			
OBSOLETE		1.800	1.400	14	30	1-102802-6			
BY 6-102802-5		1.300	.900	9	20	1-102802-5			
BY 6-102802-4	1.100	.700	7	16	1-102802-4				
7 OBSOLETE	1.500	1.100	11	24	1-102802-3				
4	OBSOLETE	.900	.500	5	12	1-102802-2			
	OBSOLETE	—	—	—	—	—	—		
	7 OBSOLETE	4.800	4.400	44	90	1-102802-0			
	OBSOLETE	3.300	2.900	29	60	102802-9			
	OBSOLETE	2.300	1.900	19	40	102802-8			
	OBSOLETE	3.800	3.400	34	70	102802-7			
	7 OBSOLETE	5.300	4.900	49	100	102802-6			
	OBSOLETE	4.300	3.900	39	80	102802-5			
	OBSOLETE	2.800	2.400	24	50	102802-4			
	7 OBSOLETE	2.100	1.700	17	36	102802-3			
OBSOLETE	6.300	5.900	59	120	102802-2				
	OBSOLETE	—	—	—	—	—	—		
	FINISH	”C”	”B”	”A”	NO OF POSN	PART NUMBER			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER		30MAR00		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK J. GESFORD		30MAR00			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. GESFORD		NAME	
mm		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± ± - ANGLES		PRODUCT SPEC		ASSY, HEADER, MOD II, .025 SQ POSTS .100X.100CL, DOUBLE ROW, RIGHT ANGLE WITH GUIDE PINS	
				APPLICATION SPEC			
MATERIAL		FINISH		SIZE		CAGE CODE	DRAWING NO
		SEE TABLE		A2		00779	C-102802
		WEIGHT		—		RESTRICTED TO	
		CUSTOMER DRAWING		SCALE		SHEET	REV
				4:1		1 of 1	13