


- Heatsinks f.cool
- Cases f.case
- Connectors f.con
 - Sockets
 - PCB connectors
 - Male headers
 - Female headers
 - Direct female connector
 - Jumpers
 - IDC-connectors
 - D-Sub connectors
 - Brackets for PC
 - Optoelectronics

Female headers

BL 5 36

Innenfederkontakt Oberfläche: Ni + 0,75µm Au

add to request



Features Technical Drawing Accessories / related products

no. of contacts	36
contact material	CuZn-Legierung
contact sleeve	tin-plated
surface contact / contact sleeve	Ni+4...6µm Sn
contact spring	gold-plated
inner contact spring material	CuBe-Legierung
inner contact spring surface	Ni + 0,75µm Au
Typ Innenfeder	6-Finger
plugability	□ 0,55 mm bis □ 0,65 mm Ø 0,65...0,85 mm
insertion depth	2,5 ... 6,0 mm
plug-in cross-section	square 0.635 Ø 0.65 to 0.85
insertion / extraction force	1,3 N / 0,3 N
shock resistance	50 g
vibration resistance max.	15 g
volume resistivity	≤10 mΩ
capacity between two adjacent contacts	≤ 0,3 pF
nominal current	3 A
nominal voltage	150 V DC
test voltage	1500 V
material isolation body	PA 4.6, GF
temperature range	-40 °C ... +163 °C (260 °C / 10 s)
class of flammability	UL 94 V-0
insulation resistance	>10 ¹² Ω
version	standard
connection type	soldering
reflow solderable	yes