







3X PIN
0.078 x 0.157
REF






SECTION A-A



RECOMMENDED
FRONT MOUNTING CUT-OUT





RECOMMENDED
REAR MOUNTING CUT-OUT




NOTES:

1. AGENCY IDENTIFICATION & RATING:
UL & CSA: 15A 250V
VDE: 10A, 250V
2. MEETS IEC 60320 SPECIFICATION
3. MATERIALS:
HOUSING: BLACK POLYESTER
TERMINALS: TIN PLATED COPPER ALLOY
CONTACT PINS: TIN PLATED COPPER ALLOY
4. THIS PRODUCT IS RoHS COMPLIANT.



CUSTOMER DRAWING



REV	ECO NUMBER	DATE	BY	APVD
A	26895	12/16/11	BL	TJK
REVISIONS				

UNLESS OTHERWISE SPECIFIED				
1. ALL DIMENSIONS IN INCHES				
- TWO PLACE DECIMALS ±0.02				
- THREE PLACE DECIMALS ±0.005				
DO NOT SCALE DRAWING				

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
SIZE		WIDTH		MULT		LBS/M		TEMPER	
FINISH SPEC No.					MATERIAL SPEC No.				
FIRST USED ON				SCALE 2:1		Switchcraft®			
DATE DRAWN	BY	CHKD		APVD					
11/17/11	BL	BL		TJK					
		11/17/11		11/17/11		SHEET 1 OF 1			
NAME MALE AC RECEPTACLE 0.25 FAST-ON TERMINALS, RoHS					PART No. EAC311X			REV A	