

Blade Fuse Holders - FLR PCB Fuse Holder for ATO® Style Blade Fuse Rated 80V

RoHS




PCB Fuse Holder for ATO/ FKS size fuse-links. For through hole soldering. Rated voltage 80V.

Specifications

Housing: Out of thermoplastic (UL 94-V0, heat-resistant)
Connections: Leaf spring connector systems, soldering terminals, copper alloy, tin (Sn) plated
Color: Black
Packaging:

Series	Pack Size
178.6164.0001	100
178.6164.0002	500

Dimensions in mm



Part Number	Description	Contact Temperature
178.6164.000_	Complete	max. 130°C

Corresponding fuse links see Section "Blade Fuses."