


Model 3302 Shielded Aluminum Box, Size F With BNC Females Both Ends



MATERIALS:

Shielded Housing: Extruded Aluminum, Alloy 6063-T5

Finish: Blue paint per Federal Standard 595, #25109 over primer wash per DOD-P-15328

Connector: 2 each BNC Female

Finish: Body and Fittings – Tarnish Resistant. Center Contact – Gold plated

Turret Screws: 4 each #3-30, Steel

Screws: 4 each #4-40 x 6.35 (1/4) per MS 35208-12 with clear irridite dip

Cover: 2 each, 2.03 (.080) thick Aluminum, Alloy #1100-H14

Finish: Clear anodized per MIL-A-8625

Cover Screws: 16 each #4-40 x 6.35 (1/4") Flat head per MS35109-221 with clear irridite dip

RATINGS:

Operating Temperature: -55°C to +150C (-67°F to +302°F)

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 3302

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA