

The Helawrap Cable Management System Helawrap HWPP/HWPA-V0

Features and Benefits

Helawrap is the ideal solution for bundling and protecting cables and wires in industrial as well as in home or office environments. Thanks to its special profile and handy applicator tool, Helawrap can be applied rapidly and effortlessly. The unique design allows the user to branch off cable at any point along the cover with ease. Helawrap can be removed and re-applied as often as required.

Helawrap is available in several colours, a large range of sizes covering most standard applications and in two durable materials. A handy applicator tool is always included.

Application

Helawrap is used to bundle and protect cable and wires in the electrical industry, panel building as well as machine, automotive and truck manufacturing. Helawrap in 25 metre lengths is the time-saving solution for industrial applications. Due to its excellent flame-retardant properties, Helawrap Polyamide 6 V0 is the product of choice wherever fire protection is essential, for example in mass transit.

Helawrap in practical 2 metre lengths is designed for domestic and office use. It puts an end to the cable chaos associated with PC's, TV's and Hi-Fi systems.



Complete cable management for home and office.



Helawrap, the fast and easy solution to your cable chaos, available in 2 sizes and 3 colours!

Technical Table

Article-No.	Type	Colour	Bundle Ø max.	Wall (WT)	Application Tool
HWPP 2m lengths					
161-64204	HWPP16L2	Black (BK)	16	0.80	HAT16
161-64205	HWPP16L2	Grey (GY)	16	0.80	HAT16
161-64206	HWPP16L2	Silver (SR)	16	0.80	HAT16
161-64404	HWPP25L2	Black (BK)	27	1.05	HAT25
161-64405	HWPP25L2	Grey (GY)	27	1.05	HAT25
161-64406	HWPP25L2	Silver (SR)	27	1.05	HAT25

All dimensions in mm. Subject to technical changes.



Insert one or more cables into the insertion slot of the applicator tool.



Place the applicator tool in one end of the Helawrap cable cover.



Simply slide the applicator tool through the Helawrap cover.

Material Data		
	Material	Polyamide 6 V0 (PA6V0)
	Operating Temperature	-40 °C to +90 °C, Intermittent +120 °C
	Flammability	UL94 V0



Material Data		
	Material	Polypropylene (PP)
	Operating Temperature	-60 °C to +110 °C, Intermittent +140 °C
	Flammability	UL94 HB



Cables can be branched off at any point for better, more flexible protection.

Technical Table

Article-No.	Type	Material	Colour	Bundle Ø max.	Wall (WT)	Application Tool
HWPP 25m lengths						
161-64101	HWPP8	PP	Black (BK)	9	0.75	HAT8
161-64102	HWPP8	PP	Grey (GY)	9	0.75	HAT8
161-64103	HWPP8	PP	Silver (SR)	9	0.75	HAT8
161-64104	HWPP8	PP	White (WH)	9	0.75	HAT8
161-64201	HWPP16	PP	Black (BK)	16	0.80	HAT16
161-64202	HWPP16	PP	Grey (GY)	16	0.80	HAT16
161-64203	HWPP16	PP	Silver (SR)	16	0.80	HAT16
161-64207	HWPP16	PP	White (WH)	16	0.80	HAT16
161-64301	HWPP20	PP	Black (BK)	21	0.95	HAT20
161-64302	HWPP20	PP	Grey (GY)	21	0.95	HAT20
161-64303	HWPP20	PP	Silver (SR)	21	0.95	HAT20
161-64304	HWPP20	PP	White (WH)	21	0.95	HAT20
161-64401	HWPP25	PP	Black (BK)	27	1.05	HAT25
161-64402	HWPP25	PP	Grey (GY)	27	1.05	HAT25
161-64403	HWPP25	PP	Silver (SR)	27	1.05	HAT25
161-64407	HWPP25	PP	White (WH)	27	1.05	HAT25
161-64501	HWPP30	PP	Black (BK)	32	1.30	HAT30
161-64502	HWPP30	PP	Grey (GY)	32	1.30	HAT30
161-64503	HWPP30	PP	Silver (SR)	32	1.30	HAT30
161-64504	HWPP30	PP	White (WH)	32	1.30	HAT30
HWPV-V0 25m lengths						
161-63101	HWPVAV08	PA6V0	Black (BK)	9	0.75	HAT8
161-63201	HWPVAV016	PA6V0	Black (BK)	16	0.85	HAT16
161-63301	HWPVAV020	PA6V0	Black (BK)	21	0.95	HAT20
161-63401	HWPVAV025	PA6V0	Black (BK)	27	1.05	HAT25
161-63501	HWPVAV030	PA6V0	Black (BK)	32	1.30	HAT30

All dimensions in mm. Subject to technical changes.