

638 Series Electromechanical Sealed Quartz DC Hour Meters

- 10-80 VDC Operating voltage
- Quartz accuracy
- Tamper resistant
- Sealed, waterproof
- 6 Figure display: 99999.9
- Round or rectangle bezel mounting



Rectangle Bezel
Model #638-04



Round Bezel
Model #638-01

Applications:



Material Handling



Construction Equipment



Farm Equipment



Utility Vehicles

638 Series Electromechanical Sealed Quartz DC Hour Meters


Description

M.H. Rhodes/Cramer Company offers the most accurate and long-term time keeping sealed Quartz DC Hour Meters available. This DC quartz Hour Meter has an operating range of 10-80 VDC. Models are available in the standard industry 2 screw or clip rectangular and 3 screw round mounting options. The 100% sealed case protects against tampering and environmental elements, providing years of reliable service. All models are NEMA 4X, 12 rated when mounted with optional gasket.


Dimensions



Rectangle Bezel
2 Screw or clip Mount
Model #638-04



Round Bezel
3 Screw Mount
Model #638-01



Features

- 10-80 VDC Operating voltage
- Superior Quartz accuracy
- 6 Figure measurement: 99999.9
- Waterproof, sealed from environmental elements
- Tamper resistant
- Round, rectangle, screw or clip mounting options
- UL/cUL Recognized, CE & RoHS Compliant

Options

- Wire leads
- Gasket kit (for NEMA 4X, 12 rating)
- Custom lens
- Terminal placement: up, down, straight

www.mhrrhodes-cramer.com



M.H. Rhodes/Cramer Company
105 Nutmeg Road South • South Windsor, CT 06074 USA
Toll Free: 877.684.6464 • PH: 860.291.8402 • FX: 860.620.0897