



A630 Pressure Adapter



Measurement Range

10 to 10,00 psi
1 to 700 Bar

Accuracy

± (1% of reading, + 10 psi)
± (1% of reading, + 0.5 Bar)

Adapter Output

1mVDC per 10 psi
1mVDC per 1 Bar

General Specifications

Input Connection: 1/4" NPT
Lead Length: 78" (2m)
Output Connection Type: Dual banana plug

Use This Adapter With

Most TPI brand and any competitor DMM, clamp-on or oscilloscope having the capability of measuring up to 2000mV AC/DC (2V AC/DC), 10M Ohm input impedance, and equipped with industry standard spaced input jacks 19mm on center.

Copyright © 2007 Test Products International, Inc.