



Mounting Head

T&B Catalog Number: TY533MX
UPC Number: 78621087960
Status: Active

Description:

Cable Tie 18lb 4" Ultraviolet Resistant Black Nylon with Stainless Steel Locking Device #4 Mounting Hole

Features

- Oval low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time. Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise **bundle** diameter needed.
- The Turned-up Tail orients the tie for easy assembly, making the ties easier to pick up on a flat surface. The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the **bundle** and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

General

Material	Nylon 6.6 Weather Resistant
Color	Black
Mounting Hole Size	#4

Dimension Information

Nominal Length (inches)	4
Length (inches)	4
Width (inches)	.091
Max. Wire Bundle Diameter (inches)	.625

Specifications

Temperature Rating	-40°F to 185°F
Flammability Rating	UL 94 V-2

Packaging

Order Multiple	100
Inner Package	100
Outer Package	500
Package Type	Regular
Package Height	3.4
Package Length	5.3
Package Width	4.3
T&B Sold in UOM	Each
T&B Weight Per UOM	0.11 lbs. per 100