

RAISED COVER WITH SCREWS, TYPE 4X



INDUSTRY STANDARDS

UL 508A Listed; Type 3, 3R, 4, 4X, 12, 13; File No. E54315
 cUL Listed per CSA C22.2 No 94; Type 3, 3R, 4, 4X, 12, 13; File No. E54315
 Enclosure flammability per UL 508A

NEMA/EEMAC Type 3, 3R, 4, 4X, 12, 13
 CSA File No. 217184: Type 3, 3R, 4, 4X, 12, 13
 IEC 60529, IP66
Meets NEMA Type 3RX requirements

APPLICATION

Enclosures feature a raised, overlapping-cover design that ensures a more-secure seal and offers increased internal space for mounting components. Available with removable and hinged covers for application flexibility.

SPECIFICATIONS

- Compression-molded fiberglass construction
- Overlapping solid raised-cover
- Cover fastens with screws
- Type 304 stainless steel piano hinges on hinged models
- Integral mounting brackets
- Enclosures protect equipment and operators from indirect electrical contact

FINISH

Fiberglass material is RAL 7035 light-gray inside and out. Optional steel panels are painted white. Optional stainless steel, aluminum, conductive and composite panels are unpainted.

ACCESSORIES

See also Accessories.
 H2OMIT™ Vent Drains, Type 4X
 HOL-SEALERS™ Non-Metallic Hole Seals
 Panels for Junction Boxes
 Swing-Out Panel Kit
 Terminal Block Kit Assembly for Junction Boxes Overview

MODIFICATION AND CUSTOMIZATION

Hoffman excels at modifying and customizing products to your specifications. Contact your local Hoffman sales office or distributor for complete information.

BULLETIN: HJ

Standard Product

Catalog Number	AxBxC in./mm	Door Fasteners	D in./mm	F in./mm	G in./mm	H in./mm	I in./mm	J in./mm	K in./mm	L in./mm	P in./mm	Q in./mm	W in./mm	Steel Panel	Alum Panel	Panel Size in./mm
RHJ1008HWLG	9.70 x 7.71 x 5.91 246 x 196 x 150	Hinged, 2 screws	6.86 174	6.49 165	10.75 273	6.00 152	11.51 292	4.50 114	3.15 80	11.22 285	8.25 210	6.25 159	9.22 234	A10P8	A10P8AL	8.75 x 6.88 222 x 102
RHJ1008WLG	9.70 x 7.71 x 5.91 246 x 196 x 150	4 screws	6.86 174	6.49 165	10.75 273	6.00 152	11.51 292	4.50 114	3.15 80	11.22 285	8.25 210	6.25 159	9.22 234	A10P8	A10P8AL	8.75 x 6.88 222 x 102
RHJ1210HWLG	11.68 x 9.69 x 6.16 296 x 246 x 156	Hinged, 2 screws	7.05 179	6.73 171	12.75 324	6.00 152	13.51 343	4.66 118	3.15 80	13.22 338	10.25 260	8.25 210	11.22 285	A12P10	A12P10AL	10.75 x 8.88 273 x 226
RHJ1210WLG	11.68 x 9.69 x 6.16 296 x 246 x 156	4 screws	7.05 179	6.73 171	12.75 324	6.00 152	13.51 343	4.66 118	3.15 80	13.22 338	10.25 260	8.25 210	11.22 285	A12P10	A12P10AL	10.75 x 8.88 273 x 226
RHJ1412HWLG	13.62 x 11.62 x 7.24 346 x 295 x 184	Hinged, 2 screws	8.13 207	7.81 194	14.75 375	10.00 254	15.51 394	5.63 143	3.25 82	15.22 387	12.25 311	10.25 260	13.22 336	A14P12	A14P12AL	12.75 x 10.88 324 x 276
RHJ1412WLG	13.62 x 11.62 x 7.24 346 x 295 x 184	4 screws	8.13 207	7.81 194	14.75 375	10.00 254	15.51 394	5.63 143	3.25 82	15.22 387	12.25 311	10.25 260	13.22 336	A14P12	A14P12AL	12.75 x 10.88 324 x 276
RHJ1614HWLG	15.62 x 13.62 x 7.24 396 x 346 x 184	Hinged, 2 screws	8.13 207	7.81 194	16.75 425	12.00 305	17.51 445	5.63 143	3.25 82	17.22 437	14.25 362	12.25 311	15.22 386	A16P14	A16P14AL	14.75 x 12.88 375 x 327
RHJ1614WLG	15.62 x 13.62 x 7.24 396 x 346 x 184	4 screws	8.13 207	7.81 194	16.75 425	12.00 305	17.51 445	5.63 143	3.25 82	17.22 437	14.25 362	12.24 311	15.30 289	A16P14	A16P14AL	14.75 x 12.88 375 x 327
RHJ1816HWLG	17.48 x 15.77 x 9.44 444 x 400 x 240	Hinged, 2 screws	10.25 260	10.01 254	18.75 476	12.00 305	19.51 496	7.76 197	3.25 82	19.22 488	16.25 413	14.25 362	17.22 437	A18P16	A18P16AL	16.75 x 14.88 425 x 378
RHJ1816WLG	17.48 x 15.77 x 9.44 444 x 400 x 240	4 screws	10.25 260	10.01 254	18.75 476	12.00 305	19.51 496	7.76 197	3.25 82	19.22 488	16.25 413	14.25 362	17.22 437	A18P16	A18P16AL	16.75 x 14.88 425 x 378

A x B x C are internal dimensions.

Purchase panels separately. Optional stainless steel, composite and aluminum panels are available for most sizes.

