





D



Description: BNC 3-Piece Crimp Plug, 50 Ohm, RG174, 188, 316  
 Part No: CPM8819  
 Application: For Cable RG174, 188, 316  
 Crimp Tool: 24-9912P  
 Impedance: 50 Ohms  
 Frequency Range: 0-4 GHz  
 Material: Body Zinc Nickel Plated  
 Contact Brass Gold Plated  
 Insulator Pom  
 Crimp Sleeve Brass Nickel Plated  
 Coupling Nut Zinc Nickel Plated  
 RoHS Compliance: Yes  
 Technical Detail: Refer to Emerson Document P/N 27-0000

C



### DIM OUTLINE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY JEAN.JIN	DATE 03-04-11
DECIMALS	mm	CHECKED BY JEAN.JIN	DATE 03-04-11
X	$\pm 0.5$	APPROVED BY DONALD	DATE 03-04-11
XX	$\pm 0.15$		
XXX	$\pm 0.1$		
ANGLES	$\pm 0.5^\circ$	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,  
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

DRAWING NO.

CPM8819-CUST

### REVISIONS

OFFICIAL RELEASE

01

03-05-09 Z G B Y T  
FIGURE OF CONTACT AND CRIMP  
SLEEVE ARE DIFFERENT WITH  
BEFORE;  
BODY MATERIAL:  
WAS: BRASS; IS: ZINC.  
INSULATOR MATERIAL:  
WAS: TEFILON; IS: POM.

02

03-04-11 J J D  
ECO-11-0034

### CUSTOMER COPY



Connectivity  
Solutions

TITLE  
BNC 3-Piece Crimp Plug, 50 Ohm,  
RG174, 188, 316

SHEET 1 OF 1 DRAWING NO. CPM8819-CUST SIZE A

SOLID EDGE RESELLER COMPANY

D

C

B

A