

General ordering data

Order No.	9532440000
Part designation	KDKS 1/35 DB
Version	Fuse terminal, 4 mm ² , Screw connection, Wemid, dark beige, TS 35
EAN	4032248039203
Qty.	50 pc(s).

Product notes

Function	400V
----------	------

Additional technical data

Colour of insulating material	dark beige
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	No
Installation advice	TS 35
Insulating material	Wemid
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	2
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Product family	SAK Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	Fuse terminal

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	4 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.33 mm ²
Clamping range, max.	4 mm ²
Type of connection	Screw connection
Connection direction	on side
Stripping length	8 mm
Clamping screw	M 3
Blade size	0.6 x 3.5 mm
Tightening torque range	0.5...0.8 Nm
Gauge to IEC 60947-1	A3
Solid, min.	0.5 mm ²
Solid, max.	4 mm ²
Stranded, min.	1.5 mm ²
Stranded, max.	4 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	4 mm ²
Flexible, min.	0.5 mm ²

Conductors for clamping (rated connection)

Flexible, max.	4 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	4 mm ²
Twin wire-end ferrule, min.	0.5 mm ²
Twin wire end ferrule, max.	1.5 mm ²

Dimensions

Width	8 mm
Height of lowest version	55.6 mm
Length	73.5 mm
TS 35 offset	36.5 mm

Display element

Operating voltage for display, max.	500 V
Type of voltage for indicator	AC

Fuse terminals

Cartridge fuse	G-Si. 5 x 20
Display	Without LED
Fuse holder (cartridge holder)	Pivoting
Operating voltage, max.	500
Type of voltage for indicator	AC

Rating data

Rated cross-section	4 mm ²
Rated voltage	500 V
Rated impulse voltage	6 kV
Rated current	6.3 A
Standards	IEC 60947-7-3
Current with max. conductor	6.3 A
Pollution severity	3

UL rating data

Voltage (UL)	300 V
Current (UL)	10 A
Min. cross-section (UL)	AWG 22
Max. cross-section (UL)	AWG 12

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000899
ETIM 3.0	EC000899
eClass 4.1	27-14-11-16
eClass 5.0	27-14-11-16
eClass 5.1	27-14-11-16

Classifications

Similar products

Order No.	Part designation	Version
9528110000	KDKS1 PE/35	Initiator/actuator terminal, 4 mm ² , Screw connection, Polyamide, beige, TS 35
9503310000	KDKS 1/35	Fuse terminal, 4 mm ² , Screw connection, PA 66, beige, TS 35